




Product Data Sheet

Part No. PT-1706 Non-Washable Type

PT-1706

DIMENSIONS



$\phi 16.5 \times H6.5$

Type	Unit	PT-1706
Rated Voltage Square Wave	(Vpp)	5
Operating Voltage	(Vpp)	1~20
Current Consumption	(mA)	< or = 1
Capacitance at 120 Hz	(pF)	11000±30%
Sound Output (Min)	(dB)	> or = 78
Resonant Frequency	(Hz)	4000±500
Operating Temp	(C)	-20~+60
Storage Temp	(C)	-30~+70
Weight	(g)	0.85
Dimension	mm	16.5 x H6.5
*Value applying at rated voltage		
*distance for measurement 10cm		

FREQUENCY RESPONSE

