CRYSTEK MICROWAVE
A Division of Crystek Corporation

RG-174 RF COAX CABLE ASSEMBLIES

RoHS Compliant

RG174 50 Ohm Coaxial Cables

SMA Male Straight/SMA Male Straight
SMA Male Straight/SMA Female Bulkhead
SMA Male Straight/SMA Male Right Angle
SMA Male Right Angle/SMA Male Right Angle
SMA Male Straight/BNC Male Straight
SMA / Alligator Clips
BNC / Alligator Clips
SMA / 2.1mm Adapter

Features:

Strain Relief: Adhesive shrink tubing over crimp area
Center Conductor: 26 AWG bare copper covered steel
Shielding: Tinned copper braid (90% coverage)
Insulation: Polyethylene
Jacket: Black PVC
Operating Temperature: -40°C to +85°C

SMA / SMA [Straight/Straight]

Part Number	Description	Length
CCSMA-MM-RG174-6	RG174 Shielded Cable, SMA Male/Male, Straight/Straight	6”
CCSMA-MM-RG174-12	RG174 Shielded Cable, SMA Male/Male, Straight/Straight	12”
CCSMA-MM-RG174-24	RG174 Shielded Cable, SMA Male/Male, Straight/Straight	24”
CCSMA-MM-RG174-36	RG174 Shielded Cable, SMA Male/Male, Straight/Straight	36”
CCSMA-MM-RG174-48	RG174 Shielded Cable, SMA Male/Male, Straight/Straight	48”

SMA / SMA [Straight/Right Angle]

Part Number	Description	Length
CCSMA1-MM-RG174-6	RG174 Shielded Cable, SMA Male/Male, Straight/RA	6”
CCSMA1-MM-RG174-12	RG174 Shielded Cable, SMA Male/Male, Straight/RA	12”
CCSMA1-MM-RG174-24	RG174 Shielded Cable, SMA Male/Male, Straight/RA	24”
CCSMA1-MM-RG174-36	RG174 Shielded Cable, SMA Male/Male, Straight/RA	36”

SMA / SMA [Right Angle/Right Angle]

Part Number	Description	Length
CCSMA2-MM-RG174-6	RG174 Shielded Cable, SMA Male/Male, RA/RA	6”
CCSMA2-MM-RG174-12	RG174 Shielded Cable, SMA Male/Male, RA/RA	12”
CCSMA2-MM-RG174-24	RG174 Shielded Cable, SMA Male/Male, RA/RA	24”
CCSMA2-MM-RG174-36	RG174 Shielded Cable, SMA Male/Male, RA/RA	36”

CRYSTEK MICROWAVE
A Division of Crystek Corporation

RG-174 RF COAX CABLE ASSEMBLIES

RoHS Compliant

SMA Male / SMA Female [Straight/Bulkhead]

Part Number	Description	Length
CCSMA-MFB-RG174-12	RG174 Shielded Cable, SMA Male/Female, Straight/Bulkhead	12”
CCSMA-MFB-RG174-24	RG174 Shielded Cable, SMA Male/Female, Straight/Bulkhead	24”
CCSMA-MFB-RG174-36	RG174 Shielded Cable, SMA Male/Female, Straight/Bulkhead	36”

P/N: CCBNS-MM-RG174-XX

RG174/U Cable
SMA to BNC
Male/Male
Length(in): 18, 36
Features: Strain relief to both SMA and BNC Connector

P/N: CCADP-MM-6

RG174/U Cable
SMA to 2.1 mm Adapter Plug
Male/Male
Length(in): 6
Features: Strain relief to both SMA and Plug Connector

SMA / BNC [Straight/Straight]

Part Number	Description	Length
CCBNS-MM-RG174-18	RG174 Shielded Cable, SMA/BNC Male/Male, Straight/Straight	18”
CCBNS-MM-RG174-36	RG174 Shielded Cable, SMA/BNC Male/Male, Straight/Straight	36”

SMA / 2.1mm Adapter

Part Number	Description	Length
CCADP-MM-6	RG174 Shielded Cable, SMA Male /2.1mm Adapter, Straight	6”

P/N: CCBNCCL-MC-30

RG174/U Cable
BNC to Alligator Clips
Male/Clips
Length(in): 30
Features: Strain relief to both Clip and SMA Connector

P/N: CCSMACL-MC-24

RG174/U Cable
SMA to Alligator Clips
Male/Clips
Length(in): 24
Features: Strain relief to both Clip and SMA Connector

BNC / Alligator Clips

Part Number	Description	Length
CCBNCCL-MC-30	RG174 Shielded Cable, BNC Male /Alligator Clips, Straight	30”

SMA / Alligator Clips

Part Number	Description	Length
CCSMACL-MC-24	RG174 Shielded Cable, SMA Male /Alligator Clips, Straight	24”