







SECTION B-B






MAXIMUM PCB DIMENSIONS
BOTTOM COVER MTG.

MODEL FLX4624



SECTION A-A



MODEL FLXT4624

NOTES:

- ① EXTERIOR INSERT AREA, FOR IN MOLD MODIFICATION.
- ② INTERIOR INSERT AREA, FOR IM MOLD MODIFICATION.

MODEL	① TOP COVER	② BOTTOM COVER	③ SCREW			
FLX 4624	73906-01	73907-01	60227-14			
FLXT4624	74979-01	73907-02	72565-06			

74977-00 REV B 08/98

COLOR / MAT'L CODE		
COLOR	94HB	94VD
BLACK	000	028
*GREY	001	024
*TAN	002	025
P. C. BONE	039	060

*CALL FACTORY FOR AVAILABILITY

PACINTEC®

FLX 4624

FLXT 4624

1-610-361-4200