

TITAN™ BARRIER

The TITAN™ is the recognised and well established stacking barrier from JSP. It has all the usual advantages of standard stackable systems but in addition has many unique features. The TITAN™ is an easy to use, assemble and store barrier system and is available in 2 metre or 1.5 metre lengths. The TITAN™ has undergone extensive testing:

- Sub zero impact testing
- Accelerated UV age testing
- Height including feet, 1.2m approx
- Dual colour coded systems for contractors corporate I.D.
- Flexible toggles allow courtesy boards to be attached to barrier
- JSP can customise courtesy boards to allow for both specific contractors/client identification and essential safety instruction to be displayed
- Courtesy boards can remain in place whilst the system is folded away
- Roll up flexible signs can also be used
- Metal free non metallic
- Fully recyclable

Coloured Base, hot foil embossing on rear of panel is also available, please contact JSP for further information.

**NOW WITH
CLASS 2
REFLECTIVE**

- 1 CLIPS**
Unique linking facility enabling easy connecting and new modified version gives compatibility with other styles.
- 2 REFLECTIVE PANEL**
Fully reflective panel meeting EN12899-1 requirements.
- 3 STABILITY**
H.D. foot giving excellent surface grip.
- 4 CONTRACTOR BRANDING**
Large area to allow contractor branding details to be applied.



**NEW DESIGN
ANTI-TRIP FOOT**



CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

TITAN™ BARRIERS

KBA073-000-600	2m Titan Barrier - Red	40
KBA053-000-600	1.5m Titan Barrier - Red	40
KBP073-000-600	2m Titan Barrier with Anti Trip Feet - Red	40
KBP053-000-600	1.5m Titan Barrier with Anti Trip Feet - Red	40

TITAN™ REPLACEMENT PARTS

KUV000-000-000	Pack of 10 Hinge Connectors	-
HBB500-400-101	Titan Foamex Courtesy Sign c/w 4 clips including 1 colour print	-
KUX010-000-600	Titan Replacement End Section 1.5 metre	-
KUX020-000-600	Titan Replacement End Section 2 metre	-
KET000-001-100	Titan Foot Only Standard	-
KEW000-005-300	Titan Anti Trip Foot Only	-

TITAN™ PVC SIGNS

HBN070-400-116	Flexible PVC signs 600 x 450mm - "Pedestrian Left" - 10 Pk	-
HBN080-400-116	Flexible PVC signs 600 x 450mm - "Pedestrian Right" - 10 Pk	-
HBB190-400-116	Flexible PVC signs 600 x 450mm - "Pedestrian use other Footpath" 10 Pk	-
HBN170-400-116	Flexible PVC signs 600 x 450mm - "Road Closed" - 10 Pk	-

**CUSTOMISE YOUR
TITANS TO YOUR
CORPORATE COLOURS**





NEW

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

XPANDA™ - BARRIER

Expanding barrier, easy to use and transport, flexible width, ideal for fencing off a variety of areas. Fully compatible, easily integrated into a Titan barrier system. Now easier to allow and restrict traffic, can be used alone or as part of a larger system. Ability to offer bespoke dual colour coded systems.

KAZ110-005-400	Expandable Titan Barrier 3 metre - Red / White	20
KAZ110-005-300	Expandable Titan Barrier 3 metre - Yellow / Black	20
KAZ110-005-700	Expandable Titan Barrier 3 metre - Blue / White	20
KAZ110-00N-600	Expandable Titan Barrier 3 metre - Green / White	20



WORKGATE™ SYSTEMS

New robust mini barrier designed with contractors in mind. Supplied as 3 or 4 gate versions, each gate having a chapter 8 reflective top panel, linked together with black clip on hinges. Easily folds for quick deployment and lightweight for storage and handling.

KBB023-000-600	3 Gated System - Red Panels, reflective (top)	15
KBB023-000-200	3-Gated System - Yellow Panels, reflective	15
KBB023-000-500	3-Gated System - Blue Panels, reflective	15
KBC023-000-600	4 Gated System - Red Panels, reflective (top)	12
KBC023-000-200	4-Gated System - Yellow Panels, reflective	12
KBC023-000-500	4-Gated System - Blue Panels, reflective	12
KEV000-001-100	Base to suit all of the above	-



- 1 REFLECTIVE PANEL
Fully reflective panel meeting EN12899-1 requirements
- 2 CONTRACTOR BRANDING
Large area to allow contractor branding / details to be applied
- 3 MATERIAL
Contains no metal parts
- 4 LINKING
Unique linking clip in upper and lower locations
- 5 TEMPORARY SIGNAGE
Locating holes enable courtesy or pedestrian signs to be fitted



Citadel™ Barrier - Class 2 Reflective

The Citadel is a strong and durable system designed to meet with the requirements of the French AFNOR NF P98-470 standard. This 2 metre system features gaps no larger than 30 x 23cm to prevent children from climbing through. Fitted with Class A reflective (French) or Class RI EN12899-1 reflective (UK)



NEW

CODE	DESCRIPTION	CARTON QTY
KBK073-000-600	Citadel 2 metre Barrier - Red	56
KBK079-000-600	Citadel 2 metre Barrier - Anti Trip Feet - Red	56

Barricader™ Barrier - Class 2 Reflective

The Barricader is a robust 2 Metre Barrier compliant with UK Chapter 8. It comes supplied with a Class RI EN12899-1 reflective tape for higher visibility in poor light conditions.



NEW

CODE	DESCRIPTION	CARTON QTY
KBH079-000-600	Barricader 2 metre Barrier - Red	56
KBL079-000-600	Barricader 2 metre Barrier - Anti Trip Feet - Red	56

1 FULLY RECYCLABLE

The Citadel and Barricader barrier are metal free which make them easy to recycle.

2 REDUCED GAPS

Reduced gaps in the barrier prevent the risk of children climbing through. Ideal for crowd control and temporary open access roadworks.

3 FLEXIBILITY

New foot connection system moulded in Co-Polymer Polypropylene with superior cold weather flexibility and strength.

4 COMPATIBILITY

Two foot option available compatible with existing Titan™ foot, as well as the New Anti-trip Foot design.

5 LINKING

New linking system allows connections to all other JSP barriers, including in curbs, rough terrain or uneven ground.

6 PROTECTION

Link Clip "parking" feature neatly locks the clip to the barrier body, protecting the clip from damage when not in use.

7 COURTESY BOARDS

Accepts standard 600 x 450mm courtesy boards for advertisement signage and offers 2 x mountable lamp slots for increased visibility.

8 RAIN CHANNELS

Rain channels and water holes avoid water collection when the systems are stacked.

9 STORAGE


Outstanding Pallet quantity of 56 units for a more stackable solution, reducing freight & storage costs.

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Champion Folding™ Barrier System

The New Improved Champion Barrier System offers exceptional value for money over life time use. It comes complete with galvanised nuts, bolts and washers which connect hinges, giving increased rigidity and robustness. Lamps are easily attached for additional night time visibility. It is easily squared or linear sited and folds for efficient storage. 5 standard lengths, bases to suit. Easy to site and easy to store in vehicles or depots.

KAC023-200-600	Champion Folding Barrier System 0.75 metre x 4 style	15
KAC033-200-600	Champion Folding Barrier System 1 metre x 4 style	15
KAC043-200-600	Champion Folding Barrier System 1.25 metre x 4 style	15
KAC053-200-600	Champion Folding Barrier System 1.5 metre x 4 style	15
KAC073-200-600	Champion Folding Barrier System 2 metre x 4 style	15
KEB000-100-000	Champion Folding Barrier System Base (to suit - max of 4 required)	60
KEC000-000-000	Champion Folding Barrier System Slimline Base as optional	-



NEW

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

ROADBLOC™

The NEW RoadBloc™ from JSP has been manufactured from Solathene HD. The system has been extensively trialled to ensure that it surpasses the demands and expectations bestowed on Traffic Separators by today's Traffic Management industry. Stacks of 20 RoadBlocs™ supplied securely banded.

KAV010-000-100	1m Roadbloc™ Barrier White	20
KAV010-000-600	1m Roadbloc™ Barrier Red	20
KAV033-000-100	1m Reflective Roadbloc™ White	20
KAV033-000-600	1m Reflective Roadbloc™ Red	20
KEA280-254-900	Roadbloc Board Support Post Red	-
KKV033-250-100	1m Reflective board with collars	-



1 POSITIONING & LINKING

The 45° Hinge Connection means RoadBloc™ is not limited to a straight-line connection; each barrier can swivel at its connection point up to 45° to enable 8 systems to form a circle or 'mini roundabout'. The hinge connector also allows each unit to be tilted at an angle whilst still connected. This means that the RoadBloc™ is ideal for use across uneven terrain.



2 STABILITY

The RoadBloc™ has been manufactured with water tight seams to allow water to be used as ballast instead of sand. Each unit also contains a large threaded, water tight plug which facilitates easy filling and drainage.



3 STACKING, STORAGE & TRANSPORT

The RoadBloc™ has been specifically designed to allow it to be moved either individually or when stacked, by a fork lift truck. Each Bloc features interlocking feet which allow the units to be stacked efficiently without the risk of them sliding apart. Stacks of 20 RoadBlocs™ supplied securely banded.



4 VISIBILITY

High quality, reflective can also be added for increased visibility. The reflective strips can be placed to sit within a recessed area on the top section of each unit. The recess allows the reflective added protection from the weather and other corrosive elements. There is also the option to add 1M high PVC barrier boards supported on 60mm diameter poles for increased visibility.



5 BRANDING

The standard RoadBloc™ is available in Red and White. However, bespoke colours to match specific corporate identities are also available. Each unit also contains 2 specific areas (one on each side) which can be embossed with a contractor's name, logo etc. These details are permanently moulded into each unit in bold, proud black print.



CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Moorgate™ Manhole Barrier Systems

A tough, stable and lightweight barrier system which is available either ready-assembled for immediate use or as individual panels for constructors own configuration.




KAE023-150-600	Moorgate 1000mm High Gate c/w Reflective Boards	50
KUC000-150-000	Clip for Moorgate System	-
KAF023-150-600	3-Gated Moorgate Assembled Version	15
KAG023-150-600	4-Gated Moorgate Assembled Version	12

CODE	DESCRIPTION	CARTON QTY
------	-------------	------------

Expanding Steel Barrier

A lightweight, steel, expanding barrier, easy to use and transport, flexible width, ideal for fencing off a variety of areas. Maximum expanded width - 2.25m. Minimum closed width 25cm width 39 cm depth. Height 1.22m. Easily portable at only 7.5kgs in weight.




KAS080-005-400	2.25m - Red / White	16
KAS080-005-300	2.25m - Yellow / Black	16

CONES

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Dominator™ 2 Part cones

The preferred traffic management and term maintenance two-part moulded cone with UV stabilised LDPE blow moulded top and heavy duty 100% recycled composite base. All cones come complete with Sealbrite class R1B Sleeve.



CONTACT US FOR
DETAILS OF OUR CONE
BRANDING SERVICE



JAB049-240-600	50cm/20" Sealbrite Sleeve	300
JAB049-840-600	50cm/20" Twin Des 2 Sleeves	300
JAZ069-240-600	75cm/30" Sealbrite Sleeve	125
JAZ060-840-600	75cm/30" Twin Des 2 Sleeves	125
JAB079-240-600	1 metre/39" Sealbrite Sleeve	100
JAB070-840-600	1 metre/39" Twin Des 2 Sleeves	100

One Piece Cones - Sand Weighted

One-piece cone complete with Des 2 reflective sleeve with traditional hexagonal base design. Sand weighting contained in a sealed moulded base.



JAA030-220-600	45cm/18" Sealbrite sleeve	500
JAA080-220-600	53cm/21" Des 2 sleeve	400
JAA050-220-600	60cm/24" Des 2 sleeve	200
JAA069-220-600	75cm/30" Sealbrite sleeve	150
JAA070-220-600	1Metre/39" Motorway Des 2 sleeve	100

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Cone Packs

Cones banded in packs for easier point of sale.



JAA030-220-615	45cm/18" Des 2 - Pk5	-
JAA069-220-615	75cm/30" Sealbrite sleeve - Pk5	-

RoadHog

100% recycled cone complete with reflective sleeve.



JAU030-200-600	x 45cm/18" Des 2 sleeve	300
JAU069-200-600	x 75cm/30" Sealbrite™	125

Economy Two Part Cone Range

Excellent value for money 2 part cone range.



JAC030-240-600	Quad 45cm/18" Des 2 sleeve	400
----------------	----------------------------	-----

Triangular No Waiting Cone

Mk2 No Waiting cone moulded from UV stabilised polyethylene and sand weighted.



JAD081-120-200	Mark II sand weighted	200
----------------	-----------------------	-----

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Dominator™

No Waiting Cone

Moulded from UV stabilised polyethylene and Dominator base weighted.



JAB041-640-200	50cm/20" Dominator	200
JUB041-600-000	Replacement Sleeve Only	-

Roadhog™

No Waiting Cone

100% recycled cone complete with no waiting sleeve.



JAU031-600-200	45cm/18" Cone	200
JUG031-600-000	Replacement Sleeve Only	-

Mark 4 No Waiting Cone

Mk4 No Waiting cone moulded from UV stabilised polyethylene and composite base weighted.



JBB081-140-200	No Waiting Cone	200
----------------	-----------------	-----

Sand Weighted Sports Cone

Sand weighted base for additional stability and curved top for supporting poles for sports purposes. Add appropriate number to the product code to select a colour: 02 - Yellow, 03 - Green, 05 - Blue, 06 - Red.



JCA020-02 - _00	30cm/12"	-
JCA030-02 - _00	45cm/18"	-
JCA050-02 - _00	60cm/24"	-
JCA060-02 - _00	75cm/30"	-

VERGE POSTS

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Kingham™ Verge Post

Toughened polyethylene blow moulded design with large reflective area conforming to RI EN12899-1 class R2 reflectors. Multi-purpose posts which can be used on verges or be set into hard core for car parks or similar delineation. Dimensions W150mm, H 1200mm. Weight 2.1kg.



HEV050-106-500	Kingham Verge Post	100
----------------	--------------------	-----

Churchill™ Verge Post

Sturdy blow moulded cylindrical design with hi vis reflective area conforming to RI EN12899-1 class R2 reflectors. Multi-purpose usage ranging from highway verges to hard standing area. Dimensions W125mm, H 1310mm. Weight 1.4kg.



HEV060-106-500	Churchill Verge Post	100
----------------	----------------------	-----

Wychwood™ Flexible Verge Post

Moulded spring back post with large reflective area conforming to RI EN12899-1 class R2 reflector.



HEV040-106-500	Flexible Verge Post	500
----------------	---------------------	-----

FENCING & ACCESSORIES

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Web Fencing

Extruded from UV stabilised polypropylene. 50m x 1m rolls.




HDF000-540-500	5.5kg Standard Weight Fencing Blue	60
HDF000-540-800	5.5kg Standard Weight Fencing Orange	60
HDF000-510-800	8kg Heavy Weight Fencing - Orange	50
HDF000-510-500	8kg Heavy Weight Fencing - Blue	50
HDF000-510-200	8kg Heavy Weight Fencing - Yellow	50
HDF000-510-300	8kg Heavy Weight Fencing - Green	50

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Fence Support

Designed to accommodate barrier fencing.



HDK100-000-100	White Fence Support Upright	-
JEP000-000-800	Orange sand weighted base	-

Black Bodyline Base


Heavy duty 100% recycled PVC base giving added stability.



KEQ000-000-000	Black bodyline base	-
----------------	---------------------	---

Metal Fencing Pin

For use with web fencing or as a general fencing aid.



HDL181-100-010	1.2cm x 13.7cm 10 per pack	-
----------------	----------------------------	---

POST AND CHAIN

CODE	DESCRIPTION	PALLET QTY
------	-------------	------------

Post and Chain - Posts

Extended posts complete with chain support cap.



HDE100-005-400	White/red	-
HDE100-005-300	Black/Yellow	-
HDE100-005-700	Blue/White	-

Post and Chain - Bases

Choose between standard or heavy duty depending upon application.



HDE130-000-000	Standard Base - Black	-
HDE170-001-100	Heavy Duty Base - Black	-

Post and Chain - Chains

Designed for use with posts or cones to form a multi-functional barrier system. Can be fitted to matching coloured posts with base. Ideal as a crowd channeliser, or to cordon off an area. Suitable for warehouses, factories, hospitals, colleges, receptions, and offices.



HDC000-275-400	8mm chain - 25m Pk - Red/White	-
HDC000-275-300	8mm chain - 25m Pk - Black/Yellow	-
HDC000-265-400	6mm chain - 25m Pk - Red/White	-
HDC000-265-300	6mm chain - 25m Pk - Black/Yellow	-

TRAFFIC MANAGEMENT - BELT BARRIERS, LAMPS & SPEED RAMPS

CODE	DESCRIPTION	CARTON QTY
------	-------------	------------

Zebra Tape™

A range of red/white zebra tape in 4 lengths and black/yellow in 500m length only.



HDH000-505-400	Red/White - 50m x 7cm	25
HDH000-605-400	Red/White - 100m X 7cm	25
HDH001-005-400	Red/White - 500mx 7cm	25
HDH001-005-300	Black/Yellow - 500m x 7cm	25

BELT BARRIERS

Wall Mounted Retractable Belt Barrier

Retractable Belt Barriers can be used in public places as well as for use in leisure or workplace environments.



HDB801-200-600	Red	-
HDB801-200-500	Blue	-
HDB801-201-100	Black	-

Retractable Belt Barrier with Black or Chrome Post and Base

Retractable Belt Barriers can be used in public places as well as for use in leisure or workplace environments.



HDB811-200-600	Black post - Red	-
HDB811-200-500	Black post - Blue	-
HDB811-201-100	Black post - Black	-
HDB881-200-600	Chrome post - Red	-
HDB881-200-500	Chrome post - Blue	-
HDB881-201-100	Chrome post - Black	-

LAMPS

Maxilite™

Powerful twin battery lamp with 360° swivel head fitted with security bolt. Conforms to EN12352 and BS3143 Part 2.



LAA020-001-200	Maxilite - Flashing with Photocell	20
LAA010-001-200	Maxilite - Flashing Non photocell	20
LUP000-000-000	6V batteries for JSP lamps	12

CODE	DESCRIPTION	CARTON QTY
------	-------------	------------

Microlite 2

360° lens for all round light visibility. Conforms to EN12352 and BS3143 Part 2.



LEM020-001-200	Microlite - Flashing with Photocell	50
LEM010-001-200	Microlite - Flashing Non photocell	50
LUP000-000-000	6V batteries for JSP lamps	12

Warning Triangle

Provides vital warning to other drivers and can help improve safety in emergency situations.



OL WARN TRIANGLE	Warning Triangle	-
------------------	------------------	---

SPEED RAMPS

NEW

Jumbo™ Speed Ramps

Manufactured from 100% recycled PVC with integral locking facility for ease of siting and installation. Each yellow and black section has white reflectors incorporated within the leading edge. Also features an underside channel allowing for hose and/or cables to be located within. 120mm x 60mm area allows client detail to be embossed for branding and security.



HAL010-125-300	10mph 5cm/2" x 50cm/19 3/4" Pair of Speed Bumps	60
HAM000-821-100	10mph 5cm/2" x 18.5cm/7" Yellow End-caps (Pair)	-
HAM000-820-200	10mph 5cm/2" x 18.5cm/7" Black End-caps (Pair)	-
HAL010-135-300	4mph 7.5cm/3" x 50cm/19 3/4" Pair of Speed Bumps	60
HAM000-831-100	4mph 7.5cm/3" x 18cm/7 1/8" Black End-caps (Pair)	-
HAM000-830-200	4mph 7.5cm/3" x 18cm/7 1/8" Yellow Endcaps (Pair)	-

Ramp Bolts

Choice of bolt depending on ground surface application.



HAH000-000-000	Pair of concrete application fixings	-
HAJ000-000-000	Pair of asphalt application fixings	-

TEMPORARY SIGNS

CODE	DESCRIPTION	CARTON QTY
------	-------------	------------

Portaglo™ Flexible Roll Up Signs c/w Tripod and Convenient Nylon Carrying Holdall

A range of sign faces manufactured from top quality prismatic material conforming to EN12899-1 which easily attach to compact steel tripods. Fully conforms to Ch.8 requirements including when supplementary signs are added. All Products come packed in a convenient nylon carrying holdall.

HBE010-300-000	750mm Road Works Diagram 7001	1
HBE030-300-000	750mm Road Narrows Diagram 517 Reversible	1
HBE060-300-000	750mm Reversible Arrow Diagram 610	1
HBE190-400-000	600mm x 450mm Pedestrian Reversible Arrow	1
HBT000-000-000	Spare Tripod only	1

Portaglo™ Flexible Roll Up Sign Face Only

HBG010-300-000	750mm Road Works Diagram 7001	1
HBG030-300-000	750mm Road Narrows Diagram 517 Reversible	1
HBG060-300-000	750mm Reversible Arrow Diagram 610	1
HBG190-400-000	600mm x 450mm Pedestrian Reversible Arrow	1
HBG400-000-000	Supplementary Sign 'End'	1
HBG470-000-000	Supplementary Sign 'Traffic Control Ahead'	1



Portabrite™ Signs

Frames of recycled non-metallic construction accepting removable sign faces, inter-changeable, lightweight and eco-friendly. All sign faces are reflective conforming to EN12899-1.

HBQ010-300-000	750mm Road Works	1
HBQ020-300-000	750mm Road Narrows Left	1
HBQ030-300-000	750mm Road Narrows Right	1
HBQ042-100-000	750mm Arrow Left	1
HBQ052-100-000	750mm Arrow Right	1
HBQ070-400-000	600mm x 450mm Pedestrian Left	1
HBQ080-400-000	600mm x 450mm Pedestrian Right	1



Cone Signs

The cone signs are manufactured from tough but flexible polypropylene sheeting and are easy to erect on a 750mm or 1m cone. The signface reflective to BS873 Class 2. They are lightweight and offer significant space saving advantage due to their flatpack design.

HBC010-300-000	75cm/30" Road Works Diagram 7001 (564)	1
HBC020-300-000	75cm/30" n/s Narrows Diagram 517 L/H	1
HBC030-300-000	75cm/30" o/s Narrows Diagram 517 R/H	1
HBC040-300-000	75cm/30" Keep Left Diagram 610	1
HBC050-300-000	75cm/30" Keep Right Diagram 610	1
HBC070-200-000	600mm x 450mm Pedestrian Right Diagram 7017 (567)	1
HBC080-200-000	600mm x 450mm Pedestrian Right Diagram 7017 (567)	1
HBC190-400-000	600mm x 450mm Pedestrian use other footway	1



CONE ACCESSORIES

CODE	DESCRIPTION	CARTON QTY
------	-------------	------------

Chain Holder for Traffic cones

Fits on cones to be used to support chains.

JUR000-000-600	Chain Holder	-
----------------	--------------	---



CODE	DESCRIPTION	CARTON QTY
------	-------------	------------

Minilite FPC with Cone bracket and bolt

Lamp supplied with fitted bolt and separate bracket for immediate assembly onto cone.

LJH020-001-200	Minilite FPC	25
----------------	--------------	----

