

Number of contacts

9–37

Mounting height

U.S. Footprint

Stamped solder pins, angled with snap-in-clips and grounding board locks

| Identification |                                                                                          | No. of contacts | Part No.               |                  |
|----------------|------------------------------------------------------------------------------------------|-----------------|------------------------|------------------|
| D-Sub          | Performance levels<br>Explanations see page 05.04<br>Other performance levels on request |                 | Performance level<br>3 | S4 <sup>1)</sup> |
|                | Male connector<br>metal shell with dimples                                               |                 |                        |                  |
|                |                                                                                          |                 | 2.84 mm pitch          | 2.84 mm pitch    |
|                |                                                                                          | 9               | 09 68 163 781 .        | 09 68 163 581 .  |
|                |                                                                                          | 15              | 09 68 263 781 .        | 09 68 263 581 .  |
|                |                                                                                          | 25              | 09 68 363 781 .        | 09 68 363 581 .  |
|                |                                                                                          | 37              | 09 68 463 781 .        | 09 68 463 581 .  |
|                |                                                                                          |                 |                        |                  |
|                |                                                                                          |                 |                        |                  |
|                |                                                                                          |                 |                        |                  |
|                | Female connector<br>metal shell                                                          |                 |                        |                  |
|                |                                                                                          |                 | 2.84 mm pitch          | 2.84 mm pitch    |
|                |                                                                                          | 9               | 09 68 153 761 .        | 09 68 153 561 .  |
|                |                                                                                          | 15              | 09 68 253 761 .        | 09 68 253 561 .  |
|                |                                                                                          | 25              | 09 68 353 761 .        | 09 68 353 561 .  |
|                |                                                                                          | 37              | 09 68 453 761 .        | 09 68 453 561 .  |
|                |                                                                                          |                 |                        |                  |
|                |                                                                                          |                 |                        |                  |
|                |                                                                                          |                 |                        |                  |
|                |                                                                                          |                 |                        |                  |
|                | Please insert digit for flange thread or fitted female screw locks                       |                 |                        |                  |
|                | M3 ▶ 1 <sup>2)</sup>                                                                     |                 |                        |                  |
|                | 4-40 UNC ▶ 2                                                                             |                 |                        |                  |
|                | fitted screw locks 4-40 UNC ▶ 3                                                          |                 |                        |                  |
|                |                                                                                          |                 |                        |                  |

<sup>1)</sup> S4 = 0.76 µm (30 µinch) Au or PdNi equivalent

<sup>2)</sup> Not normally kept in stock