

Direct Links

Cross Reference

RoHS/LF P/N search

Document & Drawing search

Application tooling

Services

Contact us

Distributor list

Pricing request

Order samples

Literature

Brochures & catalogs

Product documentation

Technical library

Start > [Search=yae18g43f*](#) > **YAE18G43F**

YAE18G43F



YAE18G43F

16,22-18 NYLON FORK

ACTIVE

Customer Drawing

RoHS compatible

Electrical division

[Assistant](#) [Add to Favorites](#)

☒ [Email Datasheet](#)  [Print Datasheet](#)

FCI Brings You More

☒ [Contact our sales/technical support...](#)

☒ [Sample request](#)

€ [Price request](#)

Download document

Literature

[> Power solutions Product Focus](#)

[> COMPRESSION TERMINAL Brochures](#)

[> Renewable Energy Products Brochure](#)

[> EC&M Catalog](#)

[> Connector Theory and Application Brochure](#)

Application Tooling

[> Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
<u>Dimensional</u>			
Stud Hole (Size)	#6 #4		
Tongue Width (in)	0.25 in.		
Wire Insulation Grip	Yes		
Insulation Diameter (Max)	0.125 in.		
<u>Physical</u>			
Conductor Size	20 AWG 18 AWG 22 AWG 16 AWG		
Element A Index	Hand Tools		
Insulation Type	Nylon		
Color Code	Red		
Conductor Size (Range)	22 AWG to 16 AWG		
<u>Approvals / Certifications</u>			
Military Listed	No		
UL Listed	No		
CSA Certified	No		
<u>Other Features</u>			
Tape Mounted Catalog Number	YAE18G43FM		
Tongue Type	Fork		
Bulk Catalog Number	YAE18G43F		
UPC	78181080461		
Keyword	smlterm		