










MATING CONNECTOR INTERFACE

TYPICAL PLUG CAVITY SECTION
(DIMENSIONS REFERENCE ONLY)

RECOMMENDED CUT OUT
FOR 1.52 MAX THICK PANEL

3-DIMENSIONAL MODEL
NTS

2.13	.084	7.62	.300	31.83	1.253
1.57	.062	5.08	.200	21.97	.865
1.52	.060	5.05	.199	19.05	.750
0.64	.025	3.68	.145	18.62	.733
0.51	.020	3.18	.125	16.21	.638
0.25	.010	2.79	.110	16.13	.635
0.13	.005	2.67	.105	7.92	.312
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

770334-1

PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.13
3 PLC DEC ± -
ANGLES ± 1°0'

DR 11-4-93
K. WHITAKER

CHK 11-4-93
R. SWING

APPD 11-4-93
C. CASH

APPD 11-4-93
C. CASH

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

NYLON,UL 94V-2
NATURAL

FINISH
-

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME
PLUG,PANEL MOUNT,
4 CIRCUIT,.062 PIN AND SOCKET

SIZE
D

CAGE CODE
00779

DRAWING NO
C-770334

SCALE
5:1

SHEET
1 OF 1