

Product SKU:	C1363.41.90
Product Description:	Speaker Wire, UL Listed (Wires, Misc.) 120V max., No. of Conductors: 2, Gauge Size (AWG): 12, Conductor/Strands: 65/30, Jacket: Premium Grade PVC - Clear - 1000 Ft. Reel
Product Category:	Electronics - Special Applications - Audio, Video, and Entertainment Cable - Speaker Wire - Clear

**Product Construction:**

Conductor:	• 24 thru 12 AWG fully-annealed 1 bare, 1 tin stranded copper per ASTM B-174
Insulation/Jacket:	• Premium grade PVC

Product Specification:

No. of Conductors:	• 2
Conductor Size (AWG):	• 12
Conductor/Strands:	• 65/30
Jacket Color:	• Clear
Nominal Insulation Thickness (in):	• 0.030
Nominal Insulation Thickness (mm):	• 0.76
Nominal Outside Diameter (in):	• 0.160 x 0.335
Nominal Outside Diameter (mm):	• 4.06 x 8.51
Standard Packaging:	• 1000' Non-returnable Wood Reels
Standard Package Quantity:	• 1
UPC #:	• 079407762590

Put-up:	• 1000
SCC-14:	• 50079407762599
Cube:	• 1507.65
Weight Per Unit of Measure:	• .06
ColorOption:	• Clear

Product Information:

Applications:	• Hi-fi and stereo speaker wire • Juke boxes • Lamps • Radios • Suggested voltage rating: 120 Volts • Not for in-wall use
Compliances:	• UL Wires Misc. (UL: 120V)
Packaging:	• 1000' (305 m) Spools • 500' (152 m) Spools • Other put-ups available- consult Customer Service

Technical Specifications

[4' Carol Brand Electrical Wire Center](#)

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)



**CAROL
BRAND**