




Protection: 4 --> flash AU
6 --> 0.76 μ AU

LEAD FREE PART NUMBER

Protection: 4 --> flash AU
6 --> 0.76 μ AU

Pitch 2.76 (shell 25-37)
Pitch 2.74 (shell 09-15)

$\Phi \pm 0.13$ holes $\varnothing 0.90$ mini

± 0.10

$\Phi \pm 0.13$ $\varnothing 3.10$

1.37 (shell 09-15)
1.38 (shell 25-37)

E

B

1.42
1.42

GENERAL CHARACTERISTICS AND ROHS INFORMATION:	
SEE DRAWING C01-8646-0000	

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	MASSON	2000/07/26	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	2000/07/26			0.XX	±0.1				
Chr	LEGARE	2000/07/26			0.XXX	±0.1				
Appr	LEGARE	2000/07/26	0.X* ±2*	ECN			LS06-0097			
Product family			D-SUB			Spec ref -				
			FEMALE CONNECTOR FOR FOOT STRAIGHT SOLDER TYPE FOR			dwg no C01-8646-0717			Rev. E	
catalog no			-			CUSTOMER			sheet 1 of 1	