


**Part Number: 130071-0032**

Image not available

**Status:** Contact Molex  
**Series:** 130071  
**Category:** Industrial Cordsets  
**Old Part Number:** LCC-32303-M050

*Series image - Reference only*

**Part Detail**
**General**

<b>Status</b>	<b>Contact Molex</b>
Category	Industrial Cordsets
Series	130071
Comments	Agency Approval: QPS EX nA II C T4 U File# QFC 3303
Connector End A	Quick-Change®
Connector End B	Quick-Change®
IP Rating	IP67
Product Name	Quick-Change®
Type	Double Ended

**Physical**

Cable Diameter	11.90mm (.468")
Cable Length	5.0m
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Female
Keyway	Single
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold
Orientation	Straight
Poles	3
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	10
Wire/Cable Type	TC Direct Burial

**Electrical**

**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	30A
Voltage - Maximum	600V

**Material Info**

Old Part Number	LCC-32303-M050
UPC	78678805235

**Reference - Drawing Numbers**

Sales Drawing	SD-130071-001
---------------	---------------

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)