


TRANSITION PIECES

ISO-KF Small Flange Components


ADAPTER ISO-KF/ISO-K

	ISO-KF/ISO-K	Part No.	A
Aluminum 6082/-	40/63	212-171	40
	50/63	212-172	45
Stainless steel 303/1.4305	40/63	212-173	40
	50/63	212-174	45
	40/100	212-175	40




ADAPTER ISO-KF/CF-F

	ISO-KF/CF-F	Part No.	A	B
Stainless steel 304/1.4301	16/16	213-251	35	16
	25/16	213-252	35	16
	16/40	213-254	30	16
	25/40	213-255	30	26
	40/40	213-256	50	37
	40/63	213-259	35	41
	40/100	213-262	50	41




ADAPTER ISO-KF/VCR FEMALE

	ISO-KF/VCR	Part No.	A
Flange: Stainless steel 304/1.4301	16/ 1/4"	211-359	35.8
Nut: Stainless steel 316L/1.4435	25/ 1/4"	211-480	35.8
	25/ 1/2"	211-360	40.6
Width across flats in inch	40/ 3/4"	211-361	53.3



ADAPTER ISO-KF/VCR MALE

	ISO-KF/VCR	Part No.	A
Flange: Stainless steel 304/1.4301	16/ 1/4"	211-362	35.8
Nut: Stainless steel 316L/1.4435	25/ 1/4"	211-481	35.8
	25/ 1/2"	211-363	40.6
Width across flats in inch	40/ 3/4"	211-364	53.3




ADAPTER ISO-KF/SWAGelok

	ISO-KF/Swagelok	Part No.	A	B
Flange: Stainless steel 304/1.4301	16/6 mm	211-356 ¹⁾	37	15.3
Nut: Stainless steel 316L/1.4435	25/10 mm	211-357 ¹⁾	45	17.2
	40/16 mm	211-358 ¹⁾	53	24.4
	16/ 1/8"	211-476 ²⁾	34.5	12.7
	25/ 1/4"	211-477 ²⁾	37	15.3
	40/ 1/4"	211-478 ²⁾	37	15.3
	40/ 1/2"	211-479 ²⁾	47.5	22.8


¹⁾ Width across flats metric (SI)

²⁾ Width across flats in inch




GLASS TUBE CONNECTION

	DN ... ISO-KF	Part No.	A	B	C	D
Flange: Aluminum 6082/—	10	211-351	50	8	10	30
Sealing: Elastomer FPM	40	211-353	65	22	26	45
Tube: Glas Pyrex						




SCREW-IN FLANGE

	ISO-KF/DN	Part No.	A	B	C	D
Flange: Stainless steel 303/1.4305	10/ G 3/8"	211-366	35	15	G 3/8"	12
Sealing: Elastomer FPM	16/ G 1/2"	211-367	35	15	G 1/2"	16
	25/ G 1"	211-368	45	25	G 1"	25
Width across flats metric (SI)	40/ G 1 1/2"	211-369	50	30	G 1 1/2"	41




SCREW-ON FLANGE

	ISO-KF/DN	Part No.	A	B	C	D
Flange: Stainless steel 303/1.4305	10/ G 3/8"	211-376	35	15	G 3/8"	10
Sealing: Elastomer FPM	16/ G 1/2"	211-377	35	15	G 1/2"	15
	25/ G 1"	211-378	45	25	G 1"	24
Width across flats metric (SI)	40/ G 1 1/2"	211-379	50	30	G 1 1/2"	38




ADAPTER ISO-KF/NPT FEMALE

	ISO-KF/NPT	Part No.	A	B	C	D
Stainless steel 303	16/ 1/8"	211-566	19	10	12	1/8-27 NPT
	16/ 1/4"	211-567	19	13	15	1/4-18 NPT
	25/ 1/8"	211-569	19	10	12	1/8-27 NPT
	25/ 1/4"	211-570	19	13	15	1/4-18 NPT
	25 / 1/2"	211-571	26	18	25	1/2-14 NPT
	25 / 1"	211-572	42	24	25	1-11 1/2 NPT
	40 / 1/4"	211-574	19	13	15	1/4-18 NPT
	40 / 1/2"	211-575	26	18	25	1/2-14 NPT
Width across flats in inch	40 / 1"	211-576	26	23	41	1-11 1/2 NPT



ADAPTER ISO-KF/NPT MALE

	ISO-KF/NPT	Part No.	A	B	C	D
Stainless steel 303 / 1.4305	16/ 1/8"	211-551	40	17	5	1/8-27 NPT
	16/ 1/4"	211-552	40	22	7	1/4-18 NPT
	25/ 1/8"	211-554	40	17	5	1/8-27 NPT
	25/ 1/4"	211-555	40	22	7	1/4-18 NPT
	25 / 1/2"	211-556	50	30	14	1/2-14 NPT
	25 / 1"	211-557	60	32	25	1-11 1/2 NPT
	40 / 1/4"	211-559	40	21	7	1/4-18 NPT
	40 / 1/2"	211-560	50	30	14	1/2-14 NPT
	40 / 1"	211-561	60	33	25	1-11 1/2 NPT
	40 / 1 1/4"	211-562	50	31.5	32	1 1/4-11 1/2 NPT
	40 / 1 1/2"	211-563	50	28	32	1 1/2-11 1/2 NPT
	40 / 2"	211-564	50	27	40	2-11 1/2 NPT
Width across flats in inch						



GLOBAL HEADQUARTERS:

Two Technology Place, East Syracuse, NY 13057 USA
Tel: +1.315.434.1100 Fax: +1.315.437.3803 E-mail: reachus@inficon.com

UNITED STATES FRANCE GERMANY LIECHTENSTEIN SWITZERLAND UNITED KINGDOM CHINA JAPAN KOREA SINGAPORE TAIWAN

Visit our website for contact information and other sales offices worldwide. www.inficon.com
Due to our continuing program of product improvements, specifications are subject to change without notice.
qiba06e1-b (2007-02) ©2007 INFICON Inc.