


Dial Dimmer for LED Light Panels from Inspired LED

I. Specifications:	
Supply voltage: DC 12V	Product size: (L)61 X (W)33 X (H)32 mm
Max load current: 2 Amps	Net weight: 30g
Output: 1 channel	Working Temperature: -20~60°C
Static power consumption: < 1 Watt	
Output Power: 24 Watts	
Function: Dim LED product from 0~100% using PWM	

II. Dimmer Unit Diagram:



Single Color LED Dimmer

Universal single color LED dimmer can dim any 12VDC LED products from 0 to 100 percent using Pulse Width Modulation (PWM) circuit. Knob control for full intensity adjustment range. Maximum Load is 2 Amps

III. Safety Information:

1. Supply voltage of this product is 12 Volts DC, do not exceed
2. Shorting output wires may cause damage to dimmer
3. Always observe proper polarity when connecting power and load
4. For indoor use only – this product is not waterproof or weatherproof

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inspired LED:](#)

[4833](#)