

Feeler Gauge Sets



Each gauge comprises a set of steel tapered blades, hardened, tempered and polished, mounted in a steel case. 12.7mm width.



Metric - DIN 2275

| Length (mm) | No. Of Blades | Thickness Of Blades x 0.01 (mm)                                                | Order Code | Price Each |
|-------------|---------------|--------------------------------------------------------------------------------|------------|------------|
| 75          | 13            | 3, 4, 5, 6, 7, 8, 9, 10, 15, 20, 30, 40, 50                                    | 137-6793   |            |
| 100         | 13            | 3, 4, 5, 6, 7, 8, 9, 10, 15, 20, 30, 40, 50                                    | 137-6794   |            |
| 100         | 13            | 5, 10, 15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100                             | 137-6795   |            |
| 100         | 20            | 5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 65, 70, 75, 80, 85, 90, 95, 100 | 137-6796   |            |
| 75          | 11            | 5, 10, 15, 20, 25, 30, 40, 50, 60, 70, 80                                      | 137-6797   |            |
| 75          | 20            | 5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 65, 70, 75, 80, 85, 90, 95, 100 | 137-6798   |            |
| 150         | 13            | 5, 10, 15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100                             | 137-6799   |            |
| 150         | 20            | 5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 65, 70, 75, 80, 85, 90, 95, 100 | 137-6800   |            |
| 300         | 20            | 5, 10, 15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 65, 70, 75, 80, 85, 90, 95, 100 | 137-6878   |            |

Metric - General Purpose

| Length (mm) | No. Of Blades | Thickness Of Blades x 0.01 (mm)       | Order Code | Price Each |
|-------------|---------------|---------------------------------------|------------|------------|
| 100         | 10            | 5, 10, 15, 20, 30, 40, 50, 60, 70, 80 | 137-6801   |            |
| 150         | 10            | 5, 10, 15, 20, 30, 40, 50, 60, 70, 80 | 137-6880   |            |
| 300         | 10            | 5, 10, 15, 20, 30, 40, 50, 60, 70, 80 | 137-6877   |            |

Imperial - DIN 2275

| Length (in) | No. Of Blades | Thickness Of Blades x 0.001 (in)                                                                 | Order Code | Price Each |
|-------------|---------------|--------------------------------------------------------------------------------------------------|------------|------------|
| 3           | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25                                                               | 137-6802   |            |
| 6           | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25                                                               | 137-6803   |            |
| 3           | 17            | 1 ½, 2, 2 ½, 3, 3 ½, 4, 5, 5 ½, 6, 7, 8, 9, 10, 12, 15, 20, 25                                   | 137-6804   |            |
| 4           | 17            | 1 ½, 2, 2 ½, 3, 3 ½, 4, 5, 5 ½, 6, 7, 8, 9, 10, 12, 15, 20, 25                                   | 137-6805   |            |
| 3           | 26            | 1 ½, 2, 2 ½, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 25 | 137-6808   |            |
| 4           | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25                                                               | 137-6811   |            |

Imperial - General Purpose

495024

| Length (in) | No. Of Blades | Thickness Of Blades x 0.001 (in)   | Order Code | Price Each |
|-------------|---------------|------------------------------------|------------|------------|
| 3           | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25 | 137-6806   |            |
| 4           | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25 | 137-6807   |            |
| 6           | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25 | 137-6876   |            |
| 12          | 10            | 1 ½, 2, 3, 4, 6, 8, 10, 12, 15, 25 | 137-6879   |            |