

97 Crimp Profiles and Locators for Crimp System Pliers

Crimp die profil	Article-No.	EAN-Code	Applications	Capacity		g	
		4003773-			AWG	g	
		97 49 04	030850	non-insulated open plug-type connectors 2.8 + 4.8 mm	0.1 - 2.5 mm ²	27-13	50
		97 49 05	030867	non-insulated open plug-type connectors 4.8 + 6.3 mm	0.5 - 6.0 mm ²²	20-10	55
		97 49 06	030836	insulated terminals and plug connectors	0.5 - 6.0 mm ²	20-10	55
		97 49 16	040675	insulated terminals and plug connectors	10 / 16 mm ²	7 / 5	50
		97 49 08	030874	end sleeves (ferrules)	0.5 - 6.0 mm ²	20-10	55
		97 49 09	030881	end sleeves (ferrules)	10 / 16 / 25 mm ²	7/5/3	55
		97 49 19	030898	end sleeves (ferrules)	35 / 50 mm ²	2 / 0	65
		97 49 13	030843	non-insulated terminals and plug connectors	0.5 - 10 mm ²	20-7	55
		97 49 23	052135	non-insulated terminals and plug connectors	16 + 25 mm ²	5 + 3	55
		97 49 15	046164	lug connectors and non-insulated plug connectors 4.8 + 6.3 mm	1.25 - 2.5 mm ²	16-10	55
		97 49 20	045212	F-connectors for TV and satellite connectors	3 - 4 / 4 - 6 mm ²	12-10	
		97 49 20	045212	F-connectors for TV and satellite connectors	Ø 9.6 / SW 8.4 + 8.1 mm; Ø 7.8 / SW 7.0 mm		55
		97 49 24	030911	D-Sub-plugs	0.03 - 0.56 mm ²	32-20	45
		97 49 30	030904	non-insulated butt connectors	1.5 - 10 mm ²	15-7	55
		97 49 35	034315	spark plug connectors + distributors			55
		97 49 40	030959	Coax connectors	RG 58,59,62,71,223		60
		97 49 50	030966	Coax connectors/Car phone	RG 58,174,188,316		60
		97 49 44	041443	rolled contacts	0.14 - 1.5 mm ²	26-15	50
		97 49 54	041450	modular plugs			
		97 49 54	041450	modular plugs	0.5 - 2.5 mm ²	20-13	55
		97 49 60	030928	turned contacts (HTS + Harting)	0.14 - 4.0 mm ²	26-11	55
		97 49 61	045137	turned contacts (Harting)	1.5/2.5/4.0/6.0 mm ²	15/13/12/10	55
		97 49 64	044055	ABS connectors	- 2.5 / - 6.0 mm ²	- 13 / - 10	60
		97 49 70	030942	unshielded Western plugs	4/6/8-poles RJ 10, 11, 12, 45		60
		97 49 74	044062	unshielded Molex plugs	8-poles RJ 12 / RJ 45		55
		97 49 76	047513	shielded Stewart plugs			50
		97 49 81	042778	Harting connectors for fibre optics	SW 3.0 / Ø 3.5; SW 4.95 / Ø 6.0; SW 6.5 / Ø 7.5		55
		97 49 82	042792	Telegärtner connectors for fibre optics	SW 3.25 / Ø 3.6; SW 3.65 / Ø 4.0; SW 4.52 / Ø 5.4		55
		97 49 83	044079	ST-, SC- + STSC/K-plugs for fibre optics	SW 3.65 / Ø 4.1; SW 4.2 / Ø 4.6; SW 5.0 / Ø 6.0		55
		97 49 84	042792	Harting/Suhner connectors for fibre optics	SW 3.8 / Ø 4.5; SW 4.3 / Ø 5.2; SW 4.95 / Ø 6.0		55
		97 49 87	043331	MIC connectors for fibre optics	SW 8.7 / Ø 9.5		50
		97 49 90	031017	Locator for 97 49 60 (HTS + Harting)			70
		97 49 91	045144	Locator for 97 49 61 (Harting)			70
		97 49 93	047926	Locator for 97 49 24 (D-Sub-plugs)			70
		97 49 94	030997	Locator for 97 49 04			20
		97 49 95	031000	Locator for 97 49 05			20

up to 250 different die profiles available;
special profiles on request