



FIRE ALARM CABLE

ADDRESSABLE SYSTEMS

UL CLASSIFIED FPLP

300 VOLTS

PLENUM CABLE
NEC 760

Shielded



DESCRIPTION:

Solid soft bare copper, insulated with extruded insulation, cabled, aluminum mylar shield, tinned copper drain wire, overall jacket

COLOR CODE: Black, White

OLYMPIC NO.	NO. OF COND.	CONDUCTOR AWG	CONDUCTOR STRAND	NOM. O.D.
3762-725	2	18	1	.146"

Fire Protective and Signaling Circuit Cables

UL CLASSIFIED FPLP

300 VOLTS

PLENUM CABLE
NEC 760

Unshielded




DESCRIPTION:

Solid soft bare copper, insulated with extruded insulation, cabled, overall red jacket

OLYMPIC NO.	NO. OF COND.	CONDUCTOR AWG	CONDUCTOR STRAND	NOM. O.D.
3752-760	2	18	1	.139"
3754-760	4	18	1	.158"
3758-760	2	16	1	.160"
*3757-760	4	16	1	.189"
3784-760A	2	14	1	.210"
3119T	4	14	1	.247"
3122T	2	12	1	.245"
3123T	4	12	1	.290"

Shielded



DESCRIPTION:

Solid soft bare copper, insulated with extruded insulation, cabled, aluminum mylar shield, tinned copper drain wire, overall red jacket

COLOR CODE:

Black, Red, White, Green

OLYMPIC NO.	NO. OF COND.	CONDUCTOR AWG	CONDUCTOR STRAND	NOM. O.D.
3762-760	2	18	1	.146"
3774-760	4	18	1	.171"
3782-760	2	16	1	.167"
3783-760	4	16	1	.196"
3760-760	2	14	1	.193"
*3119ST	4	14	1	.245"
3124T	2	12	1	.250"

*Black, Red, Yellow, Blue