





ISOMETRIC VIEW
(Scale 7/1)





RECOMMENDED PCB LAY OUT
(GENERAL TOLERANCE : ±0.05)


NOTE

- MATERIAL
 - HEADER : LCP, GLASS DILLED, UL94V-0
HALOGEN FREE, COLOR OF NATURAL
 - CONTACT TERMINAL : COPPER-ALLOY, 0.25mm THICKNESS
- PLATING
 - CONTACT TERMINAL : TIN -PLATED
0.8μm MINIMUM TIN PLATING
- PRODUCT SPECIFICATION : PS-104238-001
- PACKAGING SPECIFICATION : PK-104238-001
- COPLANALITY OF SOLDER TAILS (PEAK TEMP. : 260°C),
BEFORE & AFTER REFLOW : 0.08 MAX.
- APPLICABLE SOLIDE WIRE RANGE :
(OUTSIDE WIRE INSULATION : 1.48mm DIAMETER MAX.)
- SOLID WIRE : AWG #26~#22



RELEASED EC NO: KOR2015-0096 DRWN: SCHONG03 2015/01/12 CHKD: SHCHU 2015/01/12 APPR: YSKIM02 2015/03/30 A	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 11:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY SCHONG03	DATE 2015/01/12	TITLE MINI LITE-TRAP CONNECTOR HEADER ASS'Y -2P					
			4 PLACES	±---	±---	CHECKED BY SHCHU	DATE 2015/01/12						
			3 PLACES	±---	±---	APPROVED BY YSKIM02	DATE 2015/03/30						
			2 PLACES	±0.15	±---								
			1 PLACE	±0.20	±---								
			0 PLACE	±---	±---								
			ANGULAR ± 3 °			MATERIAL NO. 1042380210		DOCUMENT NO. SD-104238-003		SHEET NO. 1 OF 1			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						



Section A-A



Section B-B




PLASTIC BOBBIN

NOTES

1. QUANTITY OF CONNECTORS : 2,500 PCS/REEL


2. LEAD LENGTH



3. PEELING OFF FORCE OF COVER TAPE : 0.1N~0.59N(10.2GF~60GF)

(PEELING DIRECTION AS SHOW IN FOLLOW FIG.)

PEELING OFF SPEED : 300mm/Min.(Ref.)



4. FLASH IN ANY PORTION SHOULD BE LESS THAN 0.20mm MAX.

5. UNLESS OTHERWISE SPECIFIED INNER R0.2 MAX

[TABLE]

1042380210	104238-0210	NATURAL	16.0mm	104238-9002
MATERIAL NO.	NO.	COLOR	TAPE WIDTH	EMBOSS TAPE
	CONNECTOR			

RELEASED EC NO: KOR2015-0074 DRWN: SCHONG03 CHKD: SHCHU APPR: YSKIM02 2014/12/10 2014/12/10 2014/12/11	DESCRIPTION ▽=0 ▽=0	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
					MM ONLY		5:1	METRIC				
				mm	INCH	DRAWN BY	DATE	TITLE MINI S-POKE CONN. -2P MINI LITE TRAP CONN.2CKT EMBOSSED PACKAGE molex				
			4 PLACES	± ---	± ---	SCHONG03	2014/12/10					
			3 PLACES	± ---	± ---	CHECKED BY	DATE					
			2 PLACES	± 0.15	± ---	SHCHU	2014/12/10					
			1 PLACE	± 0.20	± ---	APPROVED BY	DATE					
			0 PLACE	± ---	± ---	YSKIM02	2014/12/11					
			ANGULAR ± 1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
			DRAFT WHERE APPLICABLE		1042380210		SD-104238-004		1 OF 1			
MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								