

VGA Coax Monitor Cable, High Resolution cable with RGB coax (HD15 M/M) 75-ft.

MODEL NUMBER: **P502-075**



Highlights

- 75ft SVGA/VGA Male-Male Cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Resolutions up to 2048 X 1536

Description

Tripp Lite's 75-foot SVGA/VGA monitor replacement cable is the gold standard in video cables. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Gold plated connectors and gold plated copper contacts ensure excellent conductivity. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 male connectors are molded and have integral strain relief to ensure they last a long time.

Features

- 75ft SVGA/VGA Male-Male Cable
- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Resolutions up to 2048 X 1536
- Constructed from mini-coax (RGB) and paired video wire construction for superior signal quality.
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity.
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
Intended Application	Connecting Peripherals
Style	Monitor Cables
Display Style	Direct Connect
Model Type	VGA
Cable Type	MONITOR
INPUT	

Cable Length (ft.)	75
Cable Length (m)	22.9
UPC ASSIGNMENT	
Unit Carton UPC#	037332176547
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.