

EVERYTHING SNAPS INTO PLACE

THE PRODUCT

The EURO CASE is extremely assembly-friendly. The case shells, side panels and snap-in panels all have a strong clip together mechanism, without a single screw. It is possible to customise the EURO CASE to your own corporate appearance by selecting the side panels and snap-in panels in your company's colours.

APPLICATIONS

Peripheral equipment for computers.
Feedback control. Medical devices.

PROTECTION CLASS < IP 40

STANDARD COLOURS

- Off-white, RAL 9002 (complete cases).
- Pebble grey, RAL 7032 (side panels, handle bar and tilt foot optionally).

YOUR ADVANTAGE

Minimum amount of assembly required thanks to the special OKW snap-lock mechanism.

Injection-moulded reinforcing ribs ensure that these conveniently light cases have a high degree of torsional resistance and rigidity.

Variable case heights for individual installation configuration – depending on space requirements.


Any problems in ventilation are solved by snap-in panels with ventilation slots.

MAX. SIZE OF PCB

EURO CASES	W x D in mm case shell
42 TE	243 x 220
63 TE	350 x 220
84 TE	454 x 220

Detailed drawings see our website.

VARIABLE CASE HEIGHTS



COMPLETE ENCLOSURES*1

Height-unit	Version ventilation*2	Material Colour	Part-No. EURO CASE 42 TE width = 260 mm, depth = 250 mm			Part-No. EURO CASE 63 TE width = 367 mm, depth = 250 mm			Part-No. EURO CASE 84 TE width = 473,5 mm, depth = 250 mm		
			height	without handle	with handle	height	without handle	with handle	height	without handle	with handle
1 HE	☐	ABS, off-white	54	A 02 14 070	—	54	A 02 16 070	—			
	☐	ABS, off-white	54	A 02 14 170	—	54	A 02 16 170	—			
	☐	ABS, off-white	54	A 02 14 270	—	54	A 02 16 270	—			
2 HE	☐	ABS, off-white	98.5	A 02 24 070	A 02 24 470	98.5	A 02 26 070	A 02 26 470	100	A 02 28 070	—
	☐	ABS, off-white	98.5	A 02 24 170	A 02 24 570	98.5	A 02 26 170	A 02 26 570	100	A 02 28 170	—
	☐	ABS, off-white	98.5	A 02 24 270	A 02 24 670	98.5	A 02 26 270	A 02 26 670	100	A 02 28 270	—
3 HE	☐	ABS, off-white	143	A 02 34 070	A 02 34 470	143	A 02 36 070	A 02 36 470	144.5	A 02 38 070	A 02 38 470
	☐	ABS, off-white	143	A 02 34 170	A 02 34 570	143	A 02 36 170	A 02 36 570	144.5	A 02 38 170	A 02 38 570
	☐	ABS, off-white	143	A 02 34 270	A 02 34 670	143	A 02 36 270	A 02 36 670	144.5	A 02 38 270	A 02 38 670
4 HE	☐	ABS, off-white							189	A 02 48 070	A 02 48 470
	☐	ABS, off-white							189	A 02 48 170	A 02 48 570
	☐	ABS, off-white							189	A 02 48 270	A 02 48 670
6 HE	☐	ABS, off-white				276.5	A 02 66 070	—	278	A 02 68 070	—
	☐	ABS, off-white				276.5	A 02 66 170	—	278	A 02 68 170	—
	☐	ABS, off-white				276.5	A 02 66 270	—	278	A 02 68 270	—

SEPARATE PARTS (FOR INDIVIDUAL COMBINATIONS)


Article supply each 1 pc	Part-No. 42 TE off-white 42 TE pebble grey		Part-No. 63 TE off-white 63 TE pebble grey		Part-No. 84 TE off-white 84 TE pebble grey	
① Case shell, ABS	A 01 14 170	—	A 01 16 170	—	A 01 28 170	—
② Side panel 0,5 HE, ABS	A 01 05 270	A 01 05 280	A 01 05 270	A 01 05 280	A 01 05 270	A 01 05 280
② Side panel 1 HE, ABS	A 01 10 270	A 01 10 280	A 01 10 270	A 01 10 280	A 01 10 270	A 01 10 280
② Side panel 2 HE, ABS	A 01 20 270	A 01 20 280	A 01 20 270	A 01 20 280	A 01 20 270	A 01 20 280
② Side panel 0,5 HE for handle mounting, ABS	A 01 06 270	A 01 06 280	A 01 06 270	A 01 06 280	A 01 06 270	A 01 06 280
② Side panel 1 HE for handle mounting, ABS	A 01 11 270	A 01 11 280	A 01 11 270	A 01 11 280	A 01 11 270	A 01 11 280
② Side panel 2 HE for handle mounting, ABS	A 01 21 270	A 01 21 280	A 01 21 270	A 01 21 280	A 01 21 270	A 01 21 280
③ Snap-in panel without slots, ABS	A 01 14 370	—	A 01 16 370	—	A 01 18 370	—
④ Snap-in panel with slots, ABS	A 01 24 370	—	A 01 26 370	—	A 01 28 370	—
⑥ Snap-in panel without slots, with feet, ABS	A 01 34 370	—	A 01 36 370	—	A 01 38 370	—
⑤ Snap-in panel with slots, with feet, ABS	A 01 44 370	—	A 01 46 370	—	A 01 48 370	—
Handle bar*3, off-white, push-button off-white	A 03 44 217		A 03 46 317		A 03 48 417	
Handle bar*3, pebble grey, push-button off-white	A 03 44 218		A 03 46 318		A 03 48 418	
Handle bar*3, off-white, push-button pebble grey	A 03 44 216		A 03 46 316		A 03 48 416	
Tilt foot, ABS, off-white, snaps into the feet section	A 03 50 007		A 03 50 007		A 03 50 007	

ACCESSORIES

Article supply each 1 pc	Part-No. for EURO CASE 42 TE		Part-No. for EURO CASE 63 TE		Part-No. for EURO-CASE 84 TE	
Front / rear panel, matt anodized Al, R6 1 HE	250.8 x 46.3 x 2	A 03 14 270	357.8 x 46.3 x 2	A 03 16 370	—	—
Front / rear panel, matt anodized Al, R6 1.5 HE	250.8 x 68.5 x 2	A 03 54 270	—	—	—	—
Front / rear panel, matt anodized Al, R6 2 HE	250.8 x 90.7 x 2	A 03 24 270	357.8 x 90.7 x 2	A 03 26 370	464.3 x 90.5 x 2	A 03 28 470
Front / rear panel, matt anodized Al, R6 3 HE	250.8 x 135.2 x 2	A 03 34 270	357.8 x 135.2 x 2	A 03 36 370	464.3 x 135 x 2	A 03 38 470
Front / rear panel, matt anodized Al, R6 4 HE	—	—	—	—	464.3 x 179.3 x 2	A 03 48 470
Front / rear panel, matt anodized Al, R6 6 HE	—	—	357.8 x 268.6 x 2	A 03 66 370	464.3 x 268.1 x 2	A 03 68 470

To achieve one EURO-CASE from separate parts, for a special combination, please order:

- 2 case shells
- 4 snap-in panels
- 2 side panels (if needed)
- 1 handle bar (if needed)
- 2 tilt feet (if needed)
- 2 front/rear panels (if needed)



Explanation of the parts see order data of the separate parts in the table.

*1 front / rear panel and tilt feet must be ordered separately

*2 ventilation provided with each enclosure (snap-in panel at the base additionally with foot):

- ☐ version without ventilation slots
- ☐ version with ventilation slots at rear, top and base
- ☐ version with ventilation slots at front, rear top and base

*3 the adjustment mechanism allows increments of 30°; load capacity see Info-Box page 87, illustration no. ②.