

**Part Number: 89999-3248***Image not available*

Status: Inactive
Series: [87437](#)
Category: PCB Headers
Old Part Number: 87437-1433

*Series image - Reference only***Mates With Part(s):**
[87439](#)**Part Detail****General**

Status	Inactive
Category	PCB Headers
Series	87437
Application	Signal, Wire-to-Board

Physical

Breakaway	No
Durability (mating cycles max)	10
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel, Tube
Pitch - Mating Interface	1.50mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55°C to +105°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	3A
Voltage - Maximum	350V

Material Info

Old Part Number	87437-1433
-----------------	------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)