


Receptacle Contacts

Receptacle
1.5 x 0.63 mm,
Mates with MQS 1.5


Standard Receptacle Contacts

Wire Size Range (mm ²)	Insulation Diameter		Material and Finish	Part Numbers						
	FLK (mm)	FLR (mm)		Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator		Hand Tool 539635-1 with Die Set
								Standard	Fine Adjust	
0.35~0.50	~	1.1~1.6	tin plated	1355556-1	11,000	1355557-1	500	—	1528287	539692-2
0.75~1.50	~	1.7~2.4	tin plated	1355553-1	8,500	1355554-1	500	1426196	1528207	

Single Wire Sealing System

Wire Size Range (mm²)	Insulation Diameter		Material and Finish	Part Numbers						
	FLK (mm)	FLR (mm)		Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator		Hand Tool 539635-1 with Die Set
								Standard	Fine Adjust	
0.35–0.50	~	1.1–1.6	tin plated	1241603-1	8,500	1241604-1	500	–	1528323	539693-2
0.75–1.50	~	1.7–2.4	tin plated	1241605-1	8,500	1241606-1	500	1426403	1528227	

Clean Body

Wire Size Range (mm²)	Insulation Diameter		Material and Finish	Part Numbers						
	FLK (mm)	FLR (mm)		Strip Form	Package Quantity	Loose- Piece	Package Quantity	Applicator		Hand Tool 539635-1 with Die Set
								Standard	Fine Adjust	
0.35–0.50	–	1.1–1.6	tin plated	1452158-1	12,000	1452157-1	500	–	1528287	539692-2
0.75–1.50	–	1.7–2.4	tin plated	1241608-1	8,500	1241609-1	500	1426196	1528207	