




PC board drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P90C4PA00	D09P90C6PA00
15	39.14	33.32	25.18	25.12	19.18	D15P90C4PA00	D15P90C6PA00
25	53.03	47.04	39.12	38.84	33.12	D25P90C4PA00	D25P90C6PA00
37	69.32	63.50	55.68	55.30	49.68	D37P90C4PA00	D37P90C6PA00

gold flash 0.76» gold

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P90C4PA00LF	D09P90C6PA00LF
15	39.14	33.32	25.18	25.12	19.18	D15P90C4PA00LF	D15P90C6PA00LF
25	53.03	47.04	39.12	38.84	33.12	D25P90C4PA00LF	D25P90C6PA00LF
37	69.32	63.50	55.68	55.30	49.68	D37P90C4PA00LF	D37P90C6PA00LF

gold flash 0.76» gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com

surface		tolerance std		projection		Scale	
ISO 1302		ISO 406 ISO 1101		mm			
TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PESSON	1991-09-18	ANGULAR	±0.1		A3	
Eng	PESSON	1991-09-18	LINEAR	±0.1		2	
Chr	NIRMAL GEORGE	2009-11-24	0.xx' ±2°	0.0xx		ECN 109-0268	
Appr	SUDHIR VARMA	2009-11-24	Product family		D-SUB		Spec ref -

		MALE CONNECTOR DELTA D LOW PROFIL		C01-8646-0091		Rev.	
straight press-fit						L	
catalog no				CUSTOMER		sheet 1 of 1	



Copyright FCI.