

## Datasheet

Art.No. 92.932.3053.0

### Male connector with strain relief GST18I3S S1 ZR1 WS

Connector GST18I3, 3 pole, male, screw connection, 250 V, 20 A, colour of coding: white, colour of housing: white



Art.No.	92.932.3053.0
EAN	4015573721869
Order unit	50 pieces

### Approvals



### Technical data

#### General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pull relief	Yes
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	White
Marking of poles	
Color of housing inclusive strain relief	White

#### Connection Data

Cable diameter	10.5 mm
Cable diameter 2	6.5 mm
Connection cross section solid	2.5 mm <sup>2</sup>
Cross section solid 2	0.75 mm <sup>2</sup>
Connection cross section stranded	2.5 mm <sup>2</sup>
Cross section stranded 2	0.75 mm <sup>2</sup>
Terminations per pole	1

#### Model

Model	male
-------	------

Number of poles	3
Connection type	Screw connection
Degree of protection (IP)	IP40

### Material

Housing material	Polyamide
Halogen free	Yes
Contact material	CuZn
Insulation components continuous temperature	100 °C
Surface finish	Tin-plated

### Dimensions

Length	69.4 mm
Width	28.2 mm
Height	12.6 mm

## Drawings

