







PC card drilling dimensions(after plating) _____
(thickness 1.60±0.20mm)




Copyright FCI.

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	LEAD FREE
09	30.81	24.99	16.96	16.21	10.96	D09S24A.GL00	D09S24A.GL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.GL00	D15S24A.GL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.GL00	D25S24A.GL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.GL00	D37S24A.GL00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76µ AU

rev	ecn no	dr	date
B	-	CJA	1999/10/18
C	LS05-001	MPE	2005/01/11
D	LS05-0056	MPE	2005/06/28
E	LS06-0097	LGO	2006/07/28
F	LS08-0172	MPE	2008/08/13
G	I10-0059	NG	2010-02-23
-	-	-	-

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 	mm 	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	JOUBERT	1999/10/18	ANGULAR	LINEAR		0.X	±0.1	size A3	Scale 2	
Eng	PESSON	1999/10/18				0.XX	±0.1			
Chr	NIRMAL GEORGE	2010-02-23	0.XX' ±2°		0.XXX	±0.1	ECN	I10-0059		
Appr	SUDHIR VARMA	2010-02-23	Product family				D-SUB	Spec ref -		
			FEMALE CONNECTOR EUROPE STRAIGHT STB FOR PCB 1.60mm				no dwg		Rev.	
							C01-8646-0494		G	
catalog no			-				CUSTOMER sheet 1 of 1			