



## **DURA-MARK™ PTR2E Thermal Transfer Printer And Accessories**

### *Create a variety of high quality, custom labels*

- *It's Quick!* — Custom capability allows high quality labels to be produced in-house for medium volume applications
- Choose from an assortment of self-laminating labels, heat shrink labels, component labels and colored thermal transfer rolls
- Produces high quality, opaque thermal transfer print
- Works with most standard PC's and label printing software including **PANDUIT® PAN-MARK®** Labeling Software

## Mechanical Information

|                             |                                                                                                 |        |          |
|-----------------------------|-------------------------------------------------------------------------------------------------|--------|----------|
| <b>Print Method:</b>        | Thermal transfer and direct thermal printing                                                    |        |          |
| <b>Size:</b>                | Height:                                                                                         | 6.8"   | (173 mm) |
|                             | Width:                                                                                          | 7.9"   | (200 mm) |
|                             | Depth:                                                                                          | 9.75"  | (226 mm) |
|                             | Weight:                                                                                         | 4 lbs. | (1.8kg)  |
| <b>Print Speed:</b>         | Select constant print speeds of 1", 1.5" or 2" (25.4, 38.1, or 50.8mm) per second               |        |          |
| <b>Double Buffer:</b>       | Contains a double buffer which makes the printer capable of printing continuously from WINDOWS† |        |          |
| <b>Sensors:</b>             | See through sensor designed for die-cut labels                                                  |        |          |
| <b>Graphics Resolution:</b> | 203 dpi (8 dots/mm)                                                                             |        |          |

## Print Information

- Fonts can be printed in four directions: 0°, 90°, 180° and 270°
- Capable of reverse print, bar coding and graphics
- Prints labels up to 32" (813 mm) long with characters up to 3.5" (89 mm) high
- 4.09" (104 mm) maximum print width
- Capable of horizontal and vertical print

| Part Number       | Description                                                                                                                                    | Std. Pkg. Qty* |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| <b>PTR2E</b>      | Thermal Transfer Printer<br>Includes printer, 120 VAC Adapter, power cord and manual                                                           | 1              |
| <b>PTR2-RS</b>    | External Label Roll Stand<br>Used to rear feed labels that are not supplied on 1.00" (25.4 mm) cores                                           | 1              |
| <b>PTR-CLN</b>    | Printer Cleaning Kit<br>Contains 4 oz. (116 ml) bottle cleaning solution with MSDS, cleaning pen, 100 swabs, 12 alcohol wipes and instructions | 1              |
| <b>PTR2E-CASE</b> | Hardside Carrying Case<br>Accommodates printer, AC adapter, ribbons, printer cable, labels and tools                                           | 1              |
| <b>PTR2-AC</b>    | Replacement PTR2E 120 VAC Power Supply                                                                                                         | 1              |

\*Order number required in multiples of Std. Pkg. Qty.

†WINDOWS is a registered trademark of Microsoft Corp.

# PANDUIT® PTR2E Ribbons and Labels

## PTR2E Thermal Transfer Ribbons

Available in three types:


- **High Performance Resin Ribbons** for harsh environments  
Provide excellent durability, print quality, chemical resistance and abrasion resistance
- **Versatile Wax/Resin Hybrid Ribbons** for printing on a wide range of materials  
Provide good durability, excellent print quality, and versatility to print on a variety of Panduit labels
- **Wax Ribbons** for general purpose labeling  
Economical solution provides good print quality on self-laminating labels and heat shrink markers

| Material                            | Type of Ribbon   |     |       |
|-------------------------------------|------------------|-----|-------|
|                                     | Wax/Resin Hybrid | Wax | Resin |
| Destructible Paper                  | ◆                | ◆   |       |
| Destructible Polyethylene           | ◆                |     | ◆     |
| Heat Shrink                         | ◆                | ◆   |       |
| KAPTON <sup>▲</sup> (Polyimide)     | ◆                |     |       |
| Paper Continuous Tape               | ◆                | ◆   |       |
| Polyester                           | ◆                |     | ◆     |
| Polyester Continuous Tape           | ◆                |     | ◆     |
| Self-Laminating TEDLAR <sup>▲</sup> | ◆                | ◆   |       |
| Self-Laminating Vinyl Film          | ◆                | ◆   |       |
| TEDLAR <sup>▲</sup>                 | ◆                |     | ◆     |
| Vinyl Cloth                         | ◆                | ◆   |       |
| Vinyl Continuous Tape               | ◆                |     | ◆     |

<sup>▲</sup>KAPTON and TEDLAR are the registered trademarks of E.I. DuPont Co.

| Part Number | Material         | Width<br>In. (mm) | Height<br>Ft. (m) | Color | Std.<br>Pkg.<br>Qty.* |
|-------------|------------------|-------------------|-------------------|-------|-----------------------|
| TTRH2-BL    | Wax/Resin Hybrid | 2.52 (64.0)       | 299 (91.1)        | Black | 1                     |
| TTRH-BL     |                  | 4.33 (110.0)      | 299 (91.1)        | Black |                       |
| TTRW2-BL    | Wax              | 2.50 (63.5)       | 299 (91.1)        | Black |                       |
| TTRW-BL     |                  | 4.33 (110.0)      | 299 (91.1)        | Black |                       |
| TTR2-BL     | Resin            | 2.50 (63.5)       | 299 (91.1)        | Black |                       |
| TTR2-WH     |                  |                   | 262 (79.8)        | White |                       |
| TTR-RED     |                  | 4.33 (110.0)      | 299 (91.1)        | Red   |                       |
| TTR-GRN     |                  |                   | 299 (91.1)        | Green |                       |
| TTR-BLU     |                  |                   | 299 (91.1)        | Blue  |                       |
| TTR-BL      |                  |                   | 299 (91.1)        | Black |                       |
| TTR-WH      |                  |                   | 262 (79.8)        | White |                       |

\*Order number of ribbons required in multiples of Std. Pkg. Qty.



## Laminated Label

- Can be used for wrapping around wires or in flat applications
- Print and apply top white label and overlamine with clear bottom label
- Material: GMV3 Vinyl

| Part Number | Print-On Label Size<br>In. (mm) | Overlamine Label Size<br>In. (mm) | Labels<br>Per Row | Nominal<br>Cable O.D. Range<br>In. (mm) | Std.<br>Pkg.<br>Qty.* |
|-------------|---------------------------------|-----------------------------------|-------------------|-----------------------------------------|-----------------------|
| TTSL-2P     | 1.00 x 0.50 (25.4 x 12.7)       | 1.00 x 1.00 (25.4 x 25.4)         | 4                 | 0.16 - 0.32 (4.0 - 8.1)                 | 2500                  |
| TTSL-7P     | 2.00 x 1.00 (50.8 x 25.4)       | 2.00 x 2.94 (50.8 x 74.7)         | 2                 | 0.32 - 0.93 (8.1 - 23.7)                | 500                   |

\*Order number of labels required in multiples of Std. Pkg.

# PANDUIT® PTR2E Self-Laminating Labels



## PTR2E Self-Laminating Labels

- Designed to identify all sizes of wires and cables quickly and economically
- Overlaminates protects legends for clear, permanent identification
- Vinyl material for indoor applications and TEDLAR<sup>▲</sup> material for outdoor and high temperature applications
- Labels are on 1.0" (25.4mm) cores for PTR2E Printer
- For best results, print with TTRW-BL Wax or TTRH-BL Hybrid Ribbons

| Part Number           | Label Width x Height In. (mm) | Print-On Height In. (mm) | Labels Per Row | Nominal Cable Diameter Range In. (mm) | Print-On Area Color | Material                 | Std. Pkg. Qty.* |
|-----------------------|-------------------------------|--------------------------|----------------|---------------------------------------|---------------------|--------------------------|-----------------|
| TTSL-1 <sup>‡</sup>   | 0.50 x 1.50 (12.7 x 38.1)     | 0.50 (12.7)              | 8              | 0.16 - 0.32 (4.0 - 8.1)               | White               | GMV3 Vinyl               | 5000            |
| TTSL-53               | 0.50 x 1.50 (12.7 x 38.1)     | 0.50 (12.7)              | 8              |                                       | White               | GMT1 TEDLAR              | 5000            |
| TTSL-247              | 0.80 x 0.94 (20.3 x 23.9)     | 0.38 (9.7)               | 5              | 0.12 - 0.18 (3.0 - 4.5)               | White               | GMV3 Vinyl               | 5000            |
| TTSL-246              | 0.80 x 0.94 (20.3 x 23.9)     | 0.38 (9.7)               | 5              |                                       | White               | GMT1 TEDLAR <sup>▲</sup> | 5000            |
| TTSL-249 <sup>‡</sup> | 1.00 x 0.75 (25.4 x 19.1)     | 0.38 (9.7)               | 4              | 0.13 - 0.13 (3.0 - 3.0)               | White               | GMV3 Vinyl               | 2500            |
| TTSL-248              | 1.00 x 0.75 (25.4 x 19.1)     | 0.38 (9.7)               | 4              |                                       | White               | GMT1 TEDLAR              | 2500            |
| TTSL-251 <sup>‡</sup> | 1.00 x 0.94 (25.4 x 23.9)     | 0.38 (9.7)               | 4              | 0.12 - 0.19 (3.0 - 4.5)               | White               | GMV3 Vinyl               | 2500            |
| TTSL-250              | 1.00 x 0.94 (25.4 x 23.9)     | 0.38 (9.7)               | 4              |                                       | White               | GMT1 TEDLAR              | 2500            |
| TTSL-2 <sup>‡</sup>   | 1.00 x 1.50 (25.4 x 38.1)     | 0.50 (12.7)              | 4              | 0.16 - 0.32 (4.0 - 8.1)               | White               | GMV3 Vinyl               | 2500            |
| TTSL-54               | 1.00 x 1.50 (25.4 x 38.1)     | 0.50 (12.7)              | 4              | 0.16 - 0.32 (4.0 - 8.1)               | White               | GMT1 TEDLAR              | 2500            |
| TTSL-13               | 1.00 x 1.60 (25.4 x 40.6)     | 0.80 (20.3)              | 4              | 0.25 (6.4)                            | White               | GMV3 Vinyl               | 1000            |
| TTSL-4 <sup>‡</sup>   | 1.00 x 2.44 (25.4 x 62.0)     | 1.00 (25.4)              | 4              | 0.32 - 0.46 (8.1 - 11.6)              | White               | GMV3 Vinyl               | 1500            |
| TTSL-56               | 1.00 x 2.44 (25.4 x 62.0)     | 1.00 (25.4)              | 4              |                                       | White               | GMT1 TEDLAR              | 1500            |
| TTSL-6 <sup>‡</sup>   | 1.00 x 3.94 (25.4 x 100.1)    | 1.00 (25.4)              | 4              | 0.32 - 0.93 (8.1 - 23.7)              | White               | GMV3 Vinyl               | 1000            |
| TTSL-58               | 1.00 x 3.94 (25.4 x 100.1)    | 1.00 (25.4)              | 4              |                                       | White               | GMT1 TEDLAR              | 1000            |
| TTSL-601              | 1.50 x 2.48 (38.0 x 63.0)     | 0.75 (19.0)              | 1              | 0.24 - 0.51 (6.1 x 13.0)              | White               | GMT1 TEDLAR              | 500             |
| TTSL-600              | 1.89 x 3.17 (48.0 x 80.5)     | 0.71 (8.0)               | 1              | 0.23 - 0.78 (5.8 x 19.8)              | White               | GMV3 Vinyl               | 250             |
| TTSL-3 <sup>‡</sup>   | 2.00 x 1.50 (50.8 x 38.1)     | 0.50 (12.7)              | 2              | 0.16 - 0.32 (4.0 - 8.1)               | White               | GMV3 Vinyl               | 1000            |
| TTSL-55               | 2.00 x 1.50 (50.8 x 38.1)     | 0.50 (12.7)              | 2              | 0.16 - 0.32 (4.0 - 8.1)               | White               | GMT1 TEDLAR              | 1000            |
| TTSL-5 <sup>‡</sup>   | 2.00 x 2.44 (50.8 x 62.0)     | 1.00 (25.4)              | 2              | 0.32 - 0.46 (8.1 - 11.6)              | White               | GMV3 Vinyl               | 500             |
| TTSL-57               | 2.00 x 2.44 (50.8 x 62.0)     | 1.00 (25.4)              | 2              |                                       | White               | GMT1 TEDLAR              | 500             |
| TTSL-7                | 2.00 x 3.94 (50.8 x 100.1)    | 1.00 (25.4)              | 2              | 0.32 - 0.93 (8.1 - 23.7)              | White               | GMV3 Vinyl               | 500             |
| TTSL-59               | 2.00 x 3.94 (50.8 x 100.1)    | 1.00 (25.4)              | 2              |                                       | White               | GMT1 TEDLAR              | 500             |

\*Order number of labels required in multiples of Std. Pkg. Qty.

▲TEDLAR is the registered trademark of E.I. DuPont Co.

‡ The following parts are available with TIA Specified Color Print-On Areas:

| Print-On Area Color |            |            |            |            |            |            |            |            |
|---------------------|------------|------------|------------|------------|------------|------------|------------|------------|
| White               | Blue       | Brown      | Gray       | Green      | Orange     | Red        | Violet     | Yellow     |
| TTSL-1              | TTSL-1BU   | TTSL-1BR   | TTSL-1GR   | TTSL-1IG   | TTSL-1OR   | TTSL-1RD   | TTSL-1VL   | TTSL-1YL   |
| TTSL-2              | TTSL-2BU   | TTSL-2BR   | TTSL-2GR   | TTSL-2IG   | TTSL-2OR   | TTSL-2RD   | TTSL-2VL   | TTSL-2YL   |
| TTSL-3              | TTSL-3BU   | TTSL-3BR   | TTSL-3GR   | TTSL-3IG   | TTSL-3OR   | TTSL-3RD   | TTSL-3VL   | TTSL-3YL   |
| TTSL-4              | TTSL-4BU   | TTSL-4BR   | TTSL-4GR   | TTSL-4IG   | TTSL-4OR   | TTSL-4RD   | TTSL-4VL   | TTSL-4YL   |
| TTSL-5              | TTSL-5BU   | TTSL-5BR   | TTSL-5GR   | TTSL-5IG   | TTSL-5OR   | TTSL-5RD   | TTSL-5VL   | TTSL-5YL   |
| TTSL-6              | TTSL-6BU   | TTSL-6BR   | TTSL-6GR   | TTSL-6IG   | TTSL-6OR   | TTSL-6RD   | TTSL-6VL   | TTSL-6YL   |
| TTSL-249            | TTSL-249BU | TTSL-249BR | TTSL-249GR | TTSL-249IG | TTSL-249OR | TTSL-249RD | TTSL-249VL | TTSL-249YL |
| TTSL-251            | TTSL-251BU | TTSL-251BR | TTSL-251GR | TTSL-251IG | TTSL-251OR | TTSL-251RD | TTSL-251VL | TTSL-251YL |
| TTSL-600            | —          | —          | —          | —          | —          | —          | —          | TTSL-600Y  |

# PANDUIT® PTR2E Heat Shrink Markers



## Heat Shrink Wire and Cable Markers

- Produce durable, high quality permanent heat shrink markers
- Pre-cut tubing mounted on plastic carrier
- Flattened polyolefin material
- Service Temperature Range: -22°F to 220°F (-30°C to 105°C)
- Shrink Ratio 3:1 @ 212°F (100°C)
- Meets U.L. Standard 224 for flammability
- For best results, print with TTRW-BL Wax or TTRH-BL Hybrid Ribbon

| White<br>Part Number   | Yellow<br>Part Number | Tubing<br>Diameter<br>In. (mm) | Width<br>In. (mm) | Labels<br>Per<br>Row | Nominal<br>Cable O.D.<br>In. (mm) | Labels<br>Per<br>Roll | Std.<br>Pkg.<br>Qty.* |
|------------------------|-----------------------|--------------------------------|-------------------|----------------------|-----------------------------------|-----------------------|-----------------------|
| Standard Package Parts |                       |                                |                   |                      |                                   |                       |                       |
| LHS12W1                | LHS12Y1               | 0.13 (3.2)                     | 2.00 (50.8)       | 1                    | 0.04 - 0.13<br>(1.1 - 3.2)        | 500                   | 1                     |
| LHS12-15W1             | —                     | 0.13 (3.2)                     | 1.50 (38.1)       | 1                    |                                   | 500                   | 1                     |
| LHS12W2                | LHS12Y2               | 0.13 (3.2)                     | 1.00 (25.4)       | 2                    |                                   | 1000                  | 1                     |
| LHS12-15W2             | —                     | 0.13 (3.2)                     | 0.75 (19.1)       | 2                    |                                   | 1000                  | 1                     |
| LHS12W4                | LHS12Y4               | 0.13 (3.2)                     | 0.50 (12.7)       | 4                    |                                   | 2000                  | 1                     |
| LHS18W1                | LHS18Y1               | 0.18 (4.8)                     | 2.00 (50.8)       | 1                    | 0.06 -0.18<br>(1.6 - 4.8)         | 500                   | 1                     |
| LHS18-15W1             | —                     | 0.18 (4.8)                     | 1.50 (38.1)       | 1                    |                                   | 500                   | 1                     |
| LHS18W2                | LHS18Y2               | 0.18 (4.8)                     | 1.00 (25.4)       | 2                    |                                   | 1000                  | 1                     |
| LHS18-15W2             | —                     | 0.18 (4.8)                     | 0.75 (19.1)       | 2                    |                                   | 1000                  | 1                     |
| LHS18W4                | LHS18Y4               | 0.18 (4.8)                     | 0.50 (12.7)       | 4                    |                                   | 2000                  | 1                     |
| LHS25W1                | LHS25Y1               | 0.25 (6.4)                     | 2.00 (50.8)       | 1                    | 0.08 - 0.25<br>(2.1 - 6.4)        | 500                   | 1                     |
| LHS25-15W1             | —                     | 0.25 (6.4)                     | 1.50 (38.1)       | 1                    |                                   | 500                   | 1                     |
| LHS25W2                | LHS25Y2               | 0.25 (6.4)                     | 1.00 (25.4)       | 2                    |                                   | 1000                  | 1                     |
| LHS25-15W2             | —                     | 0.25 (6.4)                     | 0.75 (19.1)       | 2                    |                                   | 1000                  | 1                     |
| LHS25W4                | LHS25Y4               | 0.25 (6.4)                     | 0.50 (12.7)       | 4                    |                                   | 2000                  | 1                     |
| LHS38W1                | —                     | 0.38 (9.7)                     | 2.00 (50.8)       | 1                    | 0.13 - 0.38<br>(3.0 - 9.7)        | 500                   | 1                     |
| LHS38W2                | —                     | 0.38 (9.7)                     | 1.00 (25.4)       | 2                    |                                   | 1000                  | 1                     |
| LHS50W1                | LHS50Y1               | 0.50 (12.7)                    | 2.00 (50.8)       | 1                    | 0.17 - 0.50<br>(4.2 - 12.7)       | 500                   | 1                     |
| LHS50W2                | LHS50Y2               | 0.50 (12.7)                    | 1.00 (25.4)       | 2                    |                                   | 1000                  | 1                     |
| LHS100W1               | LHS100Y1              | 1.00 (25.4)                    | 2.00 (50.8)       | 1                    | 0.33 - 1.00<br>(8.4 - 25.4)       | 250                   | 1                     |
| LHS100W2               | LHS100Y2              | 1.00 (25.4)                    | 1.00 (25.4)       | 2                    |                                   | 500                   | 1                     |
| Bulk Package Parts     |                       |                                |                   |                      |                                   |                       |                       |
| LHSB12W1               | —                     | 0.13 (3.2)                     | 2.00 (50.8)       | 1                    | 0.04 - 0.13<br>(1.1 - 3.2)        | 2500                  | 1                     |
| LHSB12W2               | —                     | 0.13 (3.2)                     | 1.00 (25.4)       | 2                    |                                   | 5000                  | 1                     |
| LHSB18W1               | —                     | 0.18 (4.8)                     | 2.00 (50.8)       | 1                    | 0.06 -0.18<br>(1.6 - 4.8)         | 2500                  | 1                     |
| LHSB18W2               | —                     | 0.18 (4.8)                     | 1.00 (25.4)       | 2                    |                                   | 5000                  | 1                     |
| LHSB18W4               | —                     | 0.18 (4.8)                     | 0.50 (12.7)       | 4                    |                                   | 10,000                | 1                     |
| LHSB25W1               | —                     | 0.25 (6.4)                     | 2.00 (50.8)       | 1                    | 0.08 - 0.25<br>(2.1 - 6.4)        | 2500                  | 1                     |
| LHSB25W2               | —                     | 0.25 (6.4)                     | 1.00 (25.4)       | 2                    |                                   | 5000                  | 1                     |

\*Order number of rolls required in multiples of Std. Pkg. Qty.

## Selecting the Correct Point Size

The chart below shows the Point Size to use based on the tubing diameter and lines of text desired

| Diameter In. (mm) | Lines of Text |         |         |         |         |         |
|-------------------|---------------|---------|---------|---------|---------|---------|
|                   | 1 Line        | 2 Lines | 3 Lines | 4 Lines | 5 Lines | 6 Lines |
| 0.13 (3.3)        | 12 pt         | 6 pt    | —       | —       | —       | —       |
| 0.18 (4.6)        | 18 pt         | 10 pt   | 6 pt    | —       | —       | —       |
| 0.25 (6.4)        | 24 pt         | 12 pt   | 8 pt    | 6 pt    | —       | —       |
| 0.38 (9.7)        | 36 pt         | 18 pt   | 12 pt   | 10 pt   | 7 pt    | 6 pt    |
| 0.50 (12.7)       | 48 pt         | 24 pt   | 16 pt   | 12 pt   | 10 pt   | 8 pt    |
| 1.00 (25.4)       | 72 pt         | 48 pt   | 32 pt   | 24 pt   | 20 pt   | 16 pt   |

# PANDUIT® PTR2E Component Labels

## PTR2E Component Labels



- Sizes for electrical and electronic applications
- Available in several industrial materials
- Labels are provided on 3.0" (76.2mm) cores and must be rear fed from PTR2-RS External Roll Stand (see page 1).

| Part Number  | Width<br>In. (mm) | Height<br>In. (mm) | Material                 | Color  | Labels<br>Per<br>Row | Roll Width<br>In. (mm) | Std.<br>Pkg.<br>Qty. |
|--------------|-------------------|--------------------|--------------------------|--------|----------------------|------------------------|----------------------|
| TTC84C-2.5   | 0.25 (6.4)        | 1.44 (36.5)        | Vinyl Cloth              | White  | 7                    | 2.40 (61.0)            | 2500                 |
| TTC58Y-10    | 0.31 (7.9)        | 0.31 (7.9)         | Polyester                | White  | 5                    | 2.01 (51.1)            | 10,000               |
| TTC-CPL-.5   | 0.33 (8.4)        | 0.61 (15.5)        | Polyester                | White  | 1                    | 1.25 (31.8)            | 500                  |
| TTC2K-10     | 0.38 (9.5)        | 0.38 (9.5)         | KAPTON* (Polyimide)      | Tan    | 7                    | 3.20 (81.3)            | 10,000               |
| TTC2KW-10    | 0.38 (9.5)        | 0.38 (9.5)         | KAPTON (Polyimide)       | White  | 7                    | 3.20 (81.3)            | 10,000               |
| TTC2Y-10     | 0.38 (9.5)        | 0.38 (9.5)         | Polyester                | White  | 7                    | 3.20 (81.3)            | 10,000               |
| TTC47K-20    | 0.50 (12.7)       | 0.13 (3.2)         | KAPTON (Polyimide)       | Tan    | 5                    | 3.10 (78.7)            | 20,000               |
| TTC47KW-20   | 0.50 (12.7)       | 0.13 (3.2)         | KAPTON (Polyimide)       | White  | 5                    | 3.10 (78.7)            | 20,000               |
| TTC51Y-10    | 0.50 (12.7)       | 0.25 (6.4)         | Polyester                | White  | 5                    | 3.34 (84.8)            | 10,000               |
| TTC3K-10     | 0.50 (12.7)       | 0.44 (11.1)        | KAPTON (Polyimide)       | Tan    | 5                    | 3.35 (85.1)            | 10,000               |
| TTC3KW-10    | 0.50 (12.7)       | 0.44 (11.1)        | KAPTON (Polyimide)       | White  | 5                    | 3.35 (85.1)            | 10,000               |
| TTC3Y-10     | 0.50 (12.7)       | 0.44 (11.1)        | Polyester                | White  | 5                    | 3.35 (85.1)            | 10,000               |
| TTC3YS-10    | 0.50 (12.7)       | 0.44 (11.1)        | Polyester                | Silver | 5                    | 3.35 (85.1)            | 10,000               |
| TTC3YST-10   | 0.50 (12.7)       | 0.44 (11.1)        | Tamper Evident Polyester | Silver | 5                    | 3.35 (85.1)            | 10,000               |
| TTC45Y-1     | 0.50 (12.7)       | 0.75 (19.1)        | Polyester                | White  | 3                    | 1.90 (48.3)            | 1000                 |
| TTC45C-1     | 0.50 (12.7)       | 0.75 (19.1)        | Vinyl Cloth              | White  | 3                    | 1.90 (48.3)            | 1000                 |
| TTC85C-2.5   | 0.50 (12.7)       | 1.44 (36.5)        | Vinyl Cloth              | White  | 7                    | 4.15 (105.4)           | 2500                 |
| TTC-DS110-.5 | 0.50 (12.7)       | 7.88 (200.0)       | Polyester                | White  | 1                    | 1.25 (31.8)            | 500                  |
| TTC81K-10    | 0.65 (16.5)       | 0.20 (5.1)         | KAPTON (Polyimide)       | Tan    | 3                    | 2.25 (64.8)            | 10,000               |
| TTC81KW-10   | 0.65 (16.5)       | 0.20 (5.1)         | KAPTON (Polyimide)       | White  | 3                    | 2.25 (64.8)            | 10,000               |
| TTC81Y-10    | 0.65 (16.5)       | 0.20 (5.1)         | Polyester                | White  | 3                    | 2.25 (64.8)            | 10,000               |
| TTC81YST-10  | 0.65 (16.5)       | 0.20 (5.1)         | Tamper Evident Polyester | Silver | 3                    | 2.25 (64.8)            | 10,000               |
| TTC81T-10    | 0.65 (16.5)       | 0.20 (5.1)         | TEDLAR*                  | White  | 3                    | 2.25 (64.8)            | 10,000               |
| TTC81C-10    | 0.65 (16.5)       | 0.20 (5.1)         | Vinyl Cloth              | White  | 3                    | 2.25 (64.8)            | 10,000               |
| TTC82K-10    | 0.75 (19.1)       | 0.25 (6.4)         | KAPTON (Polyimide)       | Tan    | 3                    | 2.55 (64.8)            | 10,000               |
| TTC82KW-10   | 0.75 (19.1)       | 0.25 (6.4)         | KAPTON (Polyimide)       | White  | 3                    | 2.55 (64.8)            | 10,000               |
| TTC82Y-10    | 0.75 (19.1)       | 0.25 (6.4)         | Polyester                | White  | 3                    | 2.55 (64.8)            | 10,000               |
| TTC82YS-10   | 0.75 (19.1)       | 0.25 (6.4)         | Polyester                | Silver | 3                    | 2.55 (64.8)            | 10,000               |
| TTC82YST-10  | 0.75 (19.1)       | 0.25 (6.4)         | Tamper Evident Polyester | Silver | 3                    | 2.55 (64.8)            | 10,000               |
| TTC82T-10    | 0.75 (19.1)       | 0.25 (6.4)         | TEDLAR                   | White  | 3                    | 2.55 (64.8)            | 10,000               |
| TTC82C-10    | 0.75 (19.1)       | 0.25 (6.4)         | Vinyl Cloth              | White  | 3                    | 2.55 (64.8)            | 10,000               |
| TTC86C-10    | 0.79 (20.0)       | 0.31 (8.0)         | Vinyl Cloth              | White  | 3                    | 2.71 (69.0)            | 10,000               |
| TTC87C-2.5   | 0.80 (20.3)       | 1.44 (36.6)        | Vinyl Cloth              | White  | 3                    | 2.75 (69.9)            | 2500                 |
| TTC6K-10     | 0.90 (22.9)       | 0.25 (6.4)         | KAPTON (Polyimide)       | Tan    | 3                    | 3.35 (85.1)            | 10,000               |
| TTC6KW-10    | 0.90 (22.9)       | 0.25 (6.4)         | KAPTON (Polyimide)       | White  | 3                    | 3.35 (85.1)            | 10,000               |
| TTC6Y-10     | 0.90 (22.9)       | 0.25 (6.4)         | Polyester                | White  | 3                    | 3.35 (85.1)            | 10,000               |
| TTC6T-10     | 0.90 (22.9)       | 0.25 (6.4)         | TEDLAR                   | White  | 3                    | 3.35 (85.1)            | 10,000               |

\*KAPTON and TEDLAR are the registered trademarks of E.I. DuPont Co.

\*Order number of labels required in multiples of Std. Pkg. Qty.

# PANDUIT® PTR2E Component Labels

## PTR2E Component Labels (cont.)

| Part Number  | Width<br>In. (mm) | Height<br>In. (mm) | Material                 | Color      | Labels<br>Per<br>Row | Roll Width<br>In. (mm) | Std.<br>Pkg.<br>Qty. |
|--------------|-------------------|--------------------|--------------------------|------------|----------------------|------------------------|----------------------|
| TTC49K-10    | 1.00 (25.4)       | 0.25 (6.4)         | KAPTON* (Polyimide)      | Tan        | 3                    | 3.35 (85.1)            | 10,000               |
| TTC49KW-10   | 1.00 (25.4)       | 0.25 (6.4)         | KAPTON (Polyimide)       | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC7K-10     | 1.00 (25.4)       | 0.38 (9.5)         | KAPTON (Polyimide)       | Tan        | 3                    | 3.35 (85.1)            | 10,000               |
| TTC7KW-10    | 1.00 (25.4)       | 0.38 (9.5)         | KAPTON (Polyimide)       | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC7Y-10     | 1.00 (25.4)       | 0.38 (9.5)         | Polyester                | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC7YS-10    | 1.00 (25.4)       | 0.38 (9.5)         | Polyester                | Silver     | 3                    | 3.35 (85.1)            | 10,000               |
| TTC7C-10     | 1.00 (25.4)       | 0.38 (9.5)         | Vinyl Cloth              | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8K-10     | 1.00 (25.4)       | 0.50 (12.7)        | KAPTON (Polyimide)       | Tan        | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8KW-10    | 1.00 (25.4)       | 0.50 (12.7)        | KAPTON (Polyimide)       | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8Y-10     | 1.00 (25.4)       | 0.50 (12.7)        | Polyester                | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8YC-10    | 1.00 (25.4)       | 0.50 (12.7)        | Polyester                | Clear      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8YS-10    | 1.00 (25.4)       | 0.50 (12.7)        | Polyester                | Silver     | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8YST-10   | 1.00 (25.4)       | 0.50 (12.7)        | Tamper Evident Polyester | Silver     | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8T-10     | 1.00 (25.4)       | 0.50 (12.7)        | TEDLAR*                  | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC8C-10     | 1.00 (25.4)       | 0.50 (12.7)        | Vinyl Cloth              | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC88C-10    | 1.00 (25.4)       | 0.75 (19.1)        | Vinyl Cloth              | White      | 3                    | 3.35 (85.1)            | 10,000               |
| TTC83Y-10    | 1.25 (31.8)       | 0.38 (9.5)         | Polyester                | White      | 1                    | 1.45 (36.8)            | 10,000               |
| TTC83T-10    | 1.25 (31.8)       | 0.38 (9.5)         | TEDLAR                   | White      | 1                    | 1.45 (36.8)            | 10,000               |
| TTC-MJ-5     | 1.38 (35.1)       | 0.19 (4.8)         | Polyester                | Clear      | 1                    | 1.58 (40.0)            | 5000                 |
| TTC-MJWH-5   | 1.38 (35.1)       | 0.19 (4.8)         | Polyester                | White      | 1                    | 1.58 (40.0)            | 5000                 |
| TTC90C-10    | 1.50 (38.1)       | 0.25 (6.4)         | Vinyl Cloth              | White      | 1                    | 1.70 (43.2)            | 10,000               |
| TTC91C-10    | 1.50 (38.1)       | 0.75 (19.1)        | Vinyl Cloth              | White      | 1                    | 1.70 (43.2)            | 10,000               |
| TTC15P-2.5   | 1.50 (38.1)       | 1.00 (25.4)        | Paper                    | White      | 1                    | 1.75 (44.5)            | 2500                 |
| TTC15Y-2.5   | 1.50 (38.1)       | 1.00 (25.4)        | Polyester                | White      | 1                    | 1.75 (44.5)            | 2500                 |
| TTC17Y-2.5   | 1.63 (41.3)       | 1.25 (31.8)        | Polyester                | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC52K-10    | 1.75 (44.5)       | 0.25 (6.4)         | KAPTON (Polyimide)       | Tan        | 1                    | 1.95 (49.5)            | 10,000               |
| TTC52KW-10   | 1.75 (44.5)       | 0.25 (6.4)         | KAPTON (Polyimide)       | White      | 1                    | 1.95 (49.5)            | 10,000               |
| TTC52Y-10    | 1.75 (44.6)       | 0.25 (6.4)         | Polyester                | White      | 1                    | 1.95 (49.5)            | 10,000               |
| TTC-EFPL-1   | 1.80 (45.7)       | 0.38 (9.5)         | Polyester                | White      | 1                    | 2.00 (50.8)            | 1000                 |
| TTC-EFPLC-1  | 1.80 (45.7)       | 0.38 (9.5)         | Polyester                | Clear      | 1                    | 2.00 (50.8)            | 1000                 |
| TTC18K-2.5   | 2.00 (50.8)       | 0.25 (6.4)         | KAPTON (Polyimide)       | Tan        | 1                    | 2.20 (55.9)            | 2500                 |
| TTC18KW-2.5  | 2.00 (50.8)       | 0.25 (6.4)         | KAPTON (Polyimide)       | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC18Y-2.5   | 2.00 (50.8)       | 0.25 (6.4)         | Polyester                | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC57Y-10    | 2.00 (50.8)       | 0.38 (9.5)         | Polyester                | White      | 1                    | 2.20 (55.9)            | 10,000               |
| TTC57C-10    | 2.00 (50.8)       | 0.38 (9.5)         | Vinyl Cloth              | White      | 1                    | 2.20 (55.9)            | 10,000               |
| TTC19Y-2.5   | 2.00 (50.8)       | 0.50 (12.7)        | Polyester                | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC20P-2.5   | 2.00 (50.8)       | 1.00 (25.4)        | Paper                    | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC20Y-2.5   | 2.00 (50.8)       | 1.00 (25.4)        | Polyester                | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC20YC-2.5  | 2.00 (50.8)       | 1.00 (25.4)        | Polyester                | Clear      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC20YS-2.5  | 2.00 (50.8)       | 1.00 (25.4)        | Polyester                | Silver     | 1                    | 2.20 (55.9)            | 2500                 |
| TTC20YST-2.5 | 2.00 (50.8)       | 1.00 (25.4)        | Tamper Evident Polyester | Silver     | 1                    | 2.20 (55.9)            | 2500                 |
| TTC21P-2.5   | 2.00 (50.8)       | 1.25 (31.8)        | Paper                    | White      | 1                    | 2.20 (55.9)            | 2500                 |
| TTC73Y-5     | 2.60 (66.0)       | 0.34 (8.7)         | Polyester                | White      | 1                    | 2.80 (71.1)            | 5000                 |
| TTC73YBU-5   | 2.60 (66.0)       | 0.34 (8.7)         | Polyester                | TIA Blue   | 1                    | 2.80 (71.1)            | 5000                 |
| TTC73YGR-5   | 2.60 (66.0)       | 0.34 (8.7)         | Polyester                | TIA Green  | 1                    | 2.80 (71.1)            | 5000                 |
| TTC73YIG-5   | 2.60 (66.0)       | 0.34 (8.7)         | Polyester                | TIA Gray   | 1                    | 2.80 (71.1)            | 5000                 |
| TTC73YOR-5   | 2.60 (66.0)       | 0.34 (8.7)         | Polyester                | TIA Orange | 1                    | 2.80 (71.1)            | 5000                 |
| TTC73YYL-5   | 2.60 (66.0)       | 0.34 (8.7)         | Polyester                | TIA Yellow | 1                    | 2.80 (71.1)            | 5000                 |
| TTC22P-2.5   | 2.75 (69.9)       | 1.25 (31.8)        | Paper                    | White      | 1                    | 2.95 (74.9)            | 2500                 |
| TTC22Y-2.5   | 2.75 (69.9)       | 1.25 (31.8)        | Polyester                | White      | 1                    | 2.95 (74.9)            | 2500                 |
| TTC22YS-2.5  | 2.75 (69.9)       | 1.25 (31.8)        | Polyester                | Silver     | 1                    | 2.95 (74.9)            | 2500                 |
| TTC-EFPL10-1 | 2.90 (73.7)       | 0.30 (7.6)         | Polyester                | White      | 1                    | 3.50 (88.9)            | 1000                 |
| TTC23K-2.5   | 3.00 (76.2)       | 0.25 (6.4)         | KAPTON (Polyimide)       | Tan        | 1                    | 3.20 (81.3)            | 2500                 |
| TTC23KW-2.5  | 3.00 (76.2)       | 0.25 (6.4)         | KAPTON (Polyimide)       | White      | 1                    | 3.20 (81.3)            | 2500                 |
| TTC23Y-2.5   | 3.00 (76.2)       | 0.25 (6.4)         | Polyester                | White      | 1                    | 3.20 (81.3)            | 2500                 |
| TTC89C-10    | 3.00 (81.3)       | 0.38 (9.5)         | Vinyl Cloth              | White      | 1                    | 3.20 (81.3)            | 10,000               |

Labels are roll mounted on 3.00" (76.2mm) core

\*KAPTON and TEDLAR are the registered trademarks of E.I. DuPont Co.

\*Order number of labels required in multiples of Std. Pkg. Qty.


# PANDUIT® PTR2E Component Labels

## PTR2E Component Labels (cont.)

| Part Number  | Width<br>In. (mm) | Height<br>In. (mm) | Material                 | Color  | Labels<br>Per<br>Row | Roll Width<br>In. (mm) | Std.<br>Pkg.<br>Qty. |
|--------------|-------------------|--------------------|--------------------------|--------|----------------------|------------------------|----------------------|
| TTC46P-5     | 3.00 (76.2)       | 0.94 (23.8)        | Paper                    | White  | 1                    | 3.20 (81.3)            | 5000                 |
| TTC24P-2.5   | 3.00 (76.2)       | 1.00 (25.4)        | Paper                    | White  | 1                    | 3.20 (81.3)            | 2500                 |
| TTC24Y-2.5   | 3.00 (76.2)       | 1.00 (25.4)        | Polyester                | White  | 1                    | 3.20 (81.3)            | 2500                 |
| TTC24YC-2.5  | 3.00 (76.2)       | 1.00 (25.4)        | Polyester                | Clear  | 1                    | 3.20 (81.3)            | 2500                 |
| TTC24YS-2.5  | 3.00 (76.2)       | 1.00 (25.4)        | Polyester                | Silver | 1                    | 3.20 (81.3)            | 2500                 |
| TTC24YST-2.5 | 3.00 (76.2)       | 1.00 (25.4)        | Tamper Evident Polyester | Silver | 1                    | 3.20 (81.3)            | 2500                 |
| TTC71P-2.5   | 3.00 (76.2)       | 1.75 (44.5)        | Paper                    | White  | 1                    | 3.20 (81.3)            | 2500                 |
| TTC71Y-2.5   | 3.00 (76.2)       | 1.75 (44.5)        | Polyester                | White  | 1                    | 3.20 (81.3)            | 2500                 |
| TTC25P-1     | 3.00 (76.2)       | 2.00 (50.8)        | Paper                    | White  | 1                    | 3.20 (81.3)            | 1000                 |
| TTC25Y-1     | 3.00 (76.2)       | 2.00 (50.8)        | Polyester                | White  | 1                    | 3.20 (81.3)            | 1000                 |
| TTC25YC-1    | 3.00 (76.2)       | 2.00 (50.8)        | Polyester                | Clear  | 1                    | 3.20 (81.3)            | 1000                 |
| TTC25YS-1    | 3.00 (76.2)       | 2.00 (50.8)        | Polyester                | Silver | 1                    | 3.20 (81.3)            | 1000                 |
| TTC25YST-1   | 3.00 (76.2)       | 2.00 (50.8)        | Tamper Evident Polyester | Silver | 1                    | 3.20 (81.3)            | 1000                 |
| TTC26P-1     | 3.00 (76.2)       | 5.00 (127)         | Paper                    | White  | 1                    | 3.20 (81.3)            | 1000                 |
| TTC27Y-10    | 3.25 (82.6)       | 0.31 (7.9)         | Polyester                | White  | 1                    | 4.20 (106.7)           | 10,000               |
| TTC28Y-10    | 3.25 (82.6)       | 0.50 (12.7)        | Polyester                | White  | 1                    | 3.45 (87.6)            | 10,000               |
| TTC29Y-5     | 3.25 (82.6)       | 0.63 (15.9)        | Polyester                | White  | 1                    | 4.20 (106.7)           | 5000                 |
| TTC30Y-2.5   | 3.25 (82.6)       | 0.81 (20.6)        | Polyester                | White  | 1                    | 4.20 (106.7)           | 2500                 |
| TTC31P-1     | 3.50 (88.9)       | 1.00 (25.4)        | Paper                    | White  | 1                    | 3.75 (95.3)            | 1000                 |
| TTC31Y-1     | 3.50 (88.9)       | 1.00 (25.4)        | Polyester                | White  | 1                    | 3.75 (95.3)            | 1000                 |
| TTC32P-1     | 3.50 (88.9)       | 8.00 (203.2)       | Paper                    | White  | 1                    | 3.75 (95.3)            | 1000                 |
| TTC32Y-1     | 3.50 (88.9)       | 8.00 (203.2)       | Polyester                | White  | 1                    | 3.75 (95.3)            | 1000                 |
| TTC34P-5     | 3.63 (92.1)       | 4.22 (107.1)       | Paper                    | White  | 1                    | 3.82 (97.2)            | 500                  |
| TTC33P-5     | 3.63 (92.1)       | 5.79 (147.1)       | Paper                    | White  | 1                    | 3.82 (97.2)            | 500                  |
| TTC35P-2.5   | 4.00 (101.6)      | 1.00 (25.4)        | Paper                    | White  | 1                    | 4.20 (106.7)           | 2500                 |
| TTC35Y-2.5   | 4.00 (101.6)      | 1.00 (25.4)        | Polyester                | White  | 1                    | 4.20 (106.7)           | 2500                 |
| TTC36P-1     | 4.00 (101.6)      | 2.00 (50.8)        | Paper                    | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC36Y-1     | 4.00 (101.6)      | 2.00 (50.8)        | Polyester                | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC36YS-1    | 4.00 (101.6)      | 2.00 (50.8)        | Polyester                | Silver | 1                    | 4.20 (106.7)           | 1000                 |
| TTC37P-1     | 4.00 (101.6)      | 3.00 (76.2)        | Paper                    | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC37Y-1     | 4.00 (101.6)      | 3.00 (76.2)        | Polyester                | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC38P-1     | 4.00 (101.6)      | 4.00 (101.6)       | Paper                    | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC38Y-1     | 4.00 (101.6)      | 4.00 (101.6)       | Polyester                | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC39P-1     | 4.00 (101.6)      | 5.00 (127)         | Paper                    | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC39Y-1     | 4.00 (101.6)      | 5.00 (127)         | Polyester                | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC40P-1     | 4.00 (101.6)      | 6.00 (152.4)       | Paper                    | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC40Y-1     | 4.00 (101.6)      | 6.00 (152.4)       | Polyester                | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC41P-1     | 4.00 (101.6)      | 6.50 (165.1)       | Paper                    | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC41Y-1     | 4.00 (101.6)      | 6.50 (165.1)       | Polyester                | White  | 1                    | 4.20 (106.7)           | 1000                 |
| TTC42P-5     | 4.00 (101.6)      | 12.88 (327)        | Paper                    | White  | 1                    | 4.20 (106.7)           | 500                  |
| TTC42Y-5     | 4.00 (101.6)      | 12.88 (327)        | Polyester                | White  | 1                    | 4.20 (106.7)           | 500                  |

Labels are roll mounted on 3.00" (76.2mm) core.

\*Order number of labels required in multiples of Std. Pkg. Qty.



## PTR2E Terminal Block Labels

- Used to make on-demand terminal block label strips
- Labels are on 3.0" (76.2mm) cores and must be rear fed from PTR2-RS external stand when used with the PTR2E Printer (see page 1)
- Use *PAN-MARK®* Labeling Software to align legends perfectly with termination points

| Part Number | Width<br>In. (mm) | Height<br>In. (mm) | Material   | Color | Labels<br>Per<br>Row | Roll Width<br>In. (mm) | Std.<br>Pkg.<br>Qty. |
|-------------|-------------------|--------------------|------------|-------|----------------------|------------------------|----------------------|
| TTC74POWH-C | 0.24 (6.1)        | 100 ft (30.5 m)    | Polyolefin | White | 1                    | 1.00 (25.4)            | 1                    |
| TTC75POWH-C | 0.31 (7.9)        | 100 ft (30.5 m)    | Polyolefin | White | 1                    | 1.00 (25.4)            | 1                    |
| TTC76POWH-C | 0.38 (9.7)        | 100 ft (30.5 m)    | Polyolefin | White | 1                    | 1.00 (25.4)            | 1                    |

\*Order number of rolls required in multiples of Std. Pkg. Qty.

# PANDUIT® PTR2E Continuous Tapes



## PTR2E Continuous Tapes and Overlamine Rolls

- Available in two sizes
- Continuous rolls for printing and overlaminating available
- Rolls are supplied on 1.0" (25.4 mm) cores for use with the PTR2E Printer

| Part Number              | Roll Width In. (mm) | Roll Length Ft. (m) | Color  | Material             | Std. Pkg. Qty* |
|--------------------------|---------------------|---------------------|--------|----------------------|----------------|
| 2" (50.8 mm) Wide Rolls  |                     |                     |        |                      |                |
| TTP2-CLR                 | 2.00 (50.8)         | 100 (30.5)          | Clear  | Polyester            | 1              |
| TTV2-BLK                 | 2.00 (50.8)         | 100 (30.5)          | Black  | Vinyl                |                |
| TTV2-BLU                 | 2.00 (50.8)         | 100 (30.5)          | Blue   |                      |                |
| TTV2-BRN                 | 2.00 (50.8)         | 100 (30.5)          | Brown  |                      |                |
| TTV2-GRY                 | 2.00 (50.8)         | 100 (30.5)          | Gray   |                      |                |
| TTV2-GRN                 | 2.00 (50.8)         | 100 (30.5)          | Green  |                      |                |
| TTV2-ORG                 | 2.00 (50.8)         | 100 (30.5)          | Orange |                      |                |
| TTV2-PUR                 | 2.00 (50.8)         | 100 (30.5)          | Purple |                      |                |
| TTV2-RED                 | 2.00 (50.8)         | 100 (30.5)          | Red    |                      |                |
| TTV2-WHT                 | 2.00 (50.8)         | 100 (30.5)          | White  |                      |                |
| TTV2-YEL                 | 2.00 (50.8)         | 100 (30.5)          | Yellow |                      |                |
| TTPA2-WHT                | 2.00 (50.8)         | 125 (38.1)          | White  | Paper                |                |
| TTP2-LAM                 | 2.25 (57.1)         | 100 (30.5)          | Clear  | Polyester Overlamine |                |
| 4" (101.6 mm) Wide Rolls |                     |                     |        |                      |                |
| TTP4-CLR                 | 4.00 (101.6)        | 100 (30.5)          | Clear  | Polyester            | 1              |
| TTV4-BLK                 | 4.00 (101.6)        | 100 (30.5)          | Black  | Vinyl                |                |
| TTV4-BLU                 | 4.00 (101.6)        | 100 (30.5)          | Blue   |                      |                |
| TTV4-BRN                 | 4.00 (101.6)        | 100 (30.5)          | Brown  |                      |                |
| TTV4-GRY                 | 4.00 (101.6)        | 100 (30.5)          | Gray   |                      |                |
| TTV4-GRN                 | 4.00 (101.6)        | 100 (30.5)          | Green  |                      |                |
| TTV4-ORG                 | 4.00 (101.6)        | 100 (30.5)          | Orange |                      |                |
| TTV4-PUR                 | 4.00 (101.6)        | 100 (30.5)          | Purple |                      |                |
| TTV4-RED                 | 4.00 (101.6)        | 100 (30.5)          | Red    |                      |                |
| TTV4-WHT                 | 4.00 (101.6)        | 100 (30.5)          | White  |                      |                |
| TTV4-YEL                 | 4.00 (101.6)        | 100 (30.5)          | Yellow |                      |                |
| TTPA4-WHT                | 4.00 (101.6)        | 125 (38.1)          | White  | Paper                |                |
| TTP4-LAM                 | 4.25 (108.0)        | 100 (30.5)          | Clear  | Polyester Overlamine |                |

\*Order number of rolls required in multiples of Std. Pkg. Qty

For a copy of *PANDUIT* product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty) or contact your local authorized *PANDUIT* distributor.



PANDUIT CORP.  
Tinley Park, Illinois 60477-3091  
Customer Service: 800-777-3300  
Technical Support:  
(Labels and Safety): 866-405-6658  
(Software and Printers): 866-871-4571  
Email: [td-support@panduit.com](mailto:td-support@panduit.com)  
Internet: [www.panduit.com/eg](http://www.panduit.com/eg)



Contact your local authorized *PANDUIT* distributor for pricing. For your local Sales Office call 888-506-5400

PANDUIT CANADA  
Markham, Ontario  
Phone: 800-777-3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44 208-601-7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: (65) 6379 6700

PANDUIT JAPAN  
Tokyo, Japan  
Phone (81) (3) 3767-7011

PANDUIT LATIN AMERICA  
Jalisco, Mexico  
Phone: (52) 3 666-2501

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: (61) 3-9794 9020