

DWG. NO.
SD-54593-004

F

D





A

C

B

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:			EC NO. DRWN: CHK: APPR:			EC NO. DRWN: CHK: APPR:			EC NO. DRWN: CHK: APPR:			RELEASED:04/04/14 EC NO. J2004-3790 DRWN: M.NABEI CHK: K.TOJO APPR: M.SASAO			DESCRIPTION			MATERIAL 材料 注記参照 SEE NOTES.			GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差			SCALE 4-1			DESIGN UNITS ☒ mm ☐ INCH			 THIRD ANGLE PROJECTION			☐ mm INCH ☐ INCH ☒ mm ONLY			REVISE ON CAD ONLY					
															FINISH 仕上げ 注記参照 SEE NOTES			10 UNDER 未満			±0.2			DRAWN BY & DATE M.NABEI 04/04/14			TITLE: 2.0 I/O HAND/S TYPE PLUG HS'G ASS'Y -LEAD FREE-														
															30 OVER 以上			±0.25			CHECKED BY & DATE K.TOJO 04/04/14																				
															WIRE RANGE 適用電線範囲 注記参照 SEE NOTES			30 OVER 以上			±0.3			APPROVED BY & DATE M.SASAO 04/04/14			 MOLEX INCORPORATED			CAD FILENAME SD-54593-004.S01			MATERIAL NO. SEE CHART			DRAWING NO. SD-54593-004			SHEET NO. 1 OF 1		
															INS. RANGE 被覆外径 注記参照 SEE NOTES			ANGLE 角度			±3°			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.															SIZE B		



注記
NOTES

1. 材質
MATERIAL

ハウジング : ガラス入り耐熱樹脂 UL94V-0 色 : 黒
HOUSING : G.F. HEAT RESISTANT PLASTIC UL94V-0 COLOR : BLACK
ターミナル : りん青銅 t0.3
TERMINAL : PHOSPHOR BRONZE t0.3

2. メッキ仕様
PLATING

接点部 : 金メッキ0.3µmMIN.
CONTACT AREA : GOLD 0.3µmMIN.
下地メッキ : ニッケルメッキ2µmMIN.
UNDER-PLATING : NICKEL 2µmMIN.
結線部 : 錫メッキ1.0µmMIN.
WIRE TERMINATION AREA : TIN 1.0µmMIN.

3. 適用電線範囲 : AWG #18MAX. (回路番号1, 2, 9, 10)
AWG #22MAX. (回路番号3~8)

APPLICABLE WIRES : AWG#18 MAX.(CKT.No.1,2,9,10)
AWG#22 MAX.(CKT.No.3~8)

4. 被覆外径 : ø1.6mmMAX. (回路番号1, 2, 9, 10)
ø1.2mmMAX. (回路番号3~8)

INSULATION O.D : ø1.6 mmMAX.(CKT.No.1,2,9,10)
ø1.2 mmMAX.(CKT.No.3~8)

5. 適用シエルカバー : 58935-1028
APPLICABLE SHELL COVER : 58935-1028

6. 適用シエルボディ : 58934-1028
APPLICABLE SHELL BODY : 58934-1028

7. 本製品は 54593-1011 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54593-1011.

54593-1019	54593-**-19
MATERIAL.NO	MODEL.NO
DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	SHT REVISE ON CAD ONLY

SD-54593-004.S01