






LOC		DIST		REVISIONS			
AD	0	P	LTR	DESCRIPTION		DATE	DWN
		AD	REV	PER 0G3C-0104-01		06SEP01	RB



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.
3. TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
5. MAXIMUM DIMENSION FOR I.C. SEATING PLANE.
6. SPECIAL PACKAGING.



SECTION A-A
SCALE 10:1

SUPSD BY 390262-2	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	5-640362-1
		PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-640362-4
SUPSD BY 390262-2	TINNED	PHOS.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-640362-3
		BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-640362-2
SUPSD BY 390262-2	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-640362-1
CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.CYRUS 2-20-87	AMP Tyco Electronics Corporation Harrisburg, PA 17105	
		CHK R.MILLER 2-20-87		
DIMENSIONS: INCHES		APVD —	NAME	
		PRODUCT SPEC	SOCKET ASSY, DIP, 28 POS, DIPLOMATE DL —	
		108-1066		
		APPLICATION SPEC		
MATERIAL SEE TABLE		114-1049	SIZE: CAGE CODE: DRAWING NO:	
		WEIGHT —	A1 00779 C=640362	
		CUSTOMER DRAWING		RESTRICTED TO —
		SCALE 5:1		SHEET 1 OF 1