



CONFIGURATION: TWISTED PAIR AND ONE BY ONE
HPDB50M CN50M



MAT'L:

- 1.CABLE:UL2919,#28,25P+1+AL/MY+BRAID,O.D:9.5
INSULATION OF CONDUCTOR WITH PP(ϕ 0.75)
- 2.CONNECTORS:HPDB50M,I.D.C,W/LATCH
CN50M,BLACK
INSULATOR COLOR WITH BLACK
- 3.COPPER TAPE SIZE:
HPDB50M:(10 X 105)+(25 X 85)
CN50M:42 X 140

NOTE:

- 1.TOTAL LENGTH:3FT±1inches
CABLE CUT:3FT+5CM
- 2.COLOR:BEIGE
- 3.MOLDED TYPE
- 4.360° SOLDER
- 5.ROHS COMPLIANT

RoHS
Compliant

ITEM NO

AK-Y1202-R (3 Feet)

TITLE

Centronics 50 Pin Male to
D-Sub 50 Pin Male, Half Pitch (HP)

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED

©Copyright 2008 by Assmann Electronic Components
All International Rights Reserved