




# STS Series *Economy Grade Miniature Slide Switch*

SEE PAGE B11 FOR PRODUCT SPECIFICATIONS

## SP3T




STS1300PC



## SP3T



STS1300RA




| Model     | Plating | Slide Type  |
|-----------|---------|-------------|
| STS1300PC | Silver  | Upright     |
| STS1300RA | Silver  | Right Angle |

## SP4T



STS1400PC




| Model     | Plating | Slide Type  |
|-----------|---------|-------------|
| STS1400PC | Silver  | Upright     |
| STS1400RA | Silver  | Right Angle |

## SP4T



STS141RA



| Model    | Plating | Slide Type  |
|----------|---------|-------------|
| STS141PC | Silver  | Upright     |
| STS141RA | Silver  | Right Angle |


# Low Profile/Miniature Slide/Multi-Position STS Series

SEE PAGE B11 FOR PRODUCT SPECIFICATIONS

**SP5T**



STS151PC  
STS151RA




| Model    | Plating | Slide Type  |
|----------|---------|-------------|
| STS151PC | Silver  | Upright     |
| STS151RA | Silver  | Right Angle |

**SP6T**



STS161PC  
STS161RA



| Model    | Plating | Slide Type  |
|----------|---------|-------------|
| STS161PC | Silver  | Upright     |
| STS161RA | Silver  | Right Angle |

**DP3T**




STS2300PC

**DP4T**



STS2400PC



| Model     | Plating | Slide Type |
|-----------|---------|------------|
| STS2300PC | Silver  | Upright    |
| STS2400PC | Silver  | Upright    |

Need more technical information?  
Consult your local Augat sales office

AUGAT Inc.  
452 John L. Dietsch Blvd.  
Andover Falls, MA 02762, USA


# STS Series *Economy Grade Miniature Slide Switch*

SEE PAGE B11 FOR PRODUCT SPECIFICATIONS NOTICE: STS 2300 and 2400 are available with slotted actuators upon request.

DPDT



STSA220RA




| Model     | Plating | Slide Type  |
|-----------|---------|-------------|
| STSA220RA | Silver  | Right Angle |

DPDT



STSA220RA1




| Model      | Plating | Slide Type  |
|------------|---------|-------------|
| STSA220RA1 | Silver  | Right Angle |

DP3T



STSA230RA




| Model     | Plating | Slide Type  |
|-----------|---------|-------------|
| STSA230RA | Silver  | Right Angle |

DP3T



STSA230RA1




| Model      | Plating | Slide Type  |
|------------|---------|-------------|
| STSA230RA1 | Silver  | Right Angle |

DP6T/DP5T/DP4T/  
DP3T/DP2T



STS220PC



| Model    | Type | Dim.A      | Dim.B      | Dim.C      | Travel Max. | Pin Holes | Model    | Type | Dim.A      | Dim.B      | Dim.C    | Travel Max. | Pin Holes |
|----------|------|------------|------------|------------|-------------|-----------|----------|------|------------|------------|----------|-------------|-----------|
| STS220PC | DP2T | .512(13.0) | .295(7.50) | .098(2.50) | .098(2.50)  | 6         | STS250PC | DP5T | .807(20.5) | .591(15.0) | 5 Places | .394(10.0)  | 12        |
| STS230PC | DP3T | .610(15.5) | .394(10.0) | 3 Places   | .197(5.00)  | 8         | STS260PC | DP6T | .906(23.0) | .689(17.5) | 6 Places | .492(12.5)  | 14        |
| STS240PC | DP4T | .709(18.0) | .492(12.5) | 4 Places   | .295(7.50)  | 10        |          |      |            |            |          |             |           |