

Pulling Grips Low Tension

Flexible Eye, Single Weave, Galvanized Steel



IMPORTANT!

It is important that you read all breaking strength, safety and technical data relating to this product on pages T-17 through T-27.

Light Duty Pulling Grips are made of galvanized steel in a single weave construction. They feature a flexible eye for easy attachment to a pulling line.

Junior Pulling Grips feature a strong galvanized steel, single weave mesh. A flexible eye easily attaches to a pulling line, snake or fish tape.


Junior Grip Kit

Junior Grip Kit contains 6 grips, one of each size. Catalog number **033051114**.



Note: Refer to page T-27 for building wire selection chart.

Note: Refer to page T-26 for multiple cables in a single pulling grip.




Light Duty Grips

Cable Diameter Range Inches (cm.)	Approx. Breaking Strength Lbs. (N)	E Inches (cm)	M Inches (cm)	Catalog Numbers
Short				
.50"- .61" (1.27-1.55)	2,800 (12,454)	5" (12.70)	11" (27.94)	03303001
.62"- .74" (1.57-1.88)	2,800 (12,454)	5" (12.70)	11" (27.94)	03303002
.75"- .99" (1.90-2.51)	4,000 (17,792)	6" (15.24)	12" (30.48)	03303003
1.00"-1.24" (2.54-3.15)	5,300 (23,574)	7" (17.78)	13" (33.02)	03303004
1.25"-1.49" (3.17-3.78)	5,300 (23,574)	7" (17.78)	14" (35.56)	03303005
1.50"-1.74" (3.81-4.42)	6,800 (30,246)	8" (20.32)	15" (38.10)	03303006
1.75"-1.99" (4.44-5.05)	8,500 (37,808)	9" (22.86)	17" (43.18)	03303007
2.00"-2.49" (5.08-6.32)	8,500 (37,808)	9" (22.86)	18" (45.72)	03303008

Standard

.50"- .61" (1.27-1.55)	2,800 (12,454)	5" (12.70)	16" (40.64)	03303010
.62"- .74" (1.57-1.88)	2,800 (12,454)	5" (12.70)	16" (40.64)	03303011
.75"- .99" (1.90-2.51)	4,000 (17,792)	6" (15.24)	20" (50.80)	03303012
1.00"-1.24" (2.54-3.15)	6,800 (30,246)	7" (17.78)	20" (50.80)	03303013
1.25"-1.49" (3.17-3.78)	6,800 (30,246)	7" (17.78)	21" (53.34)	03303015
1.50"-1.99" (3.81-5.05)	6,800 (30,246)	8" (20.32)	23" (58.42)	03303016
2.00"-2.49" (5.08-6.32)	8,500 (37,808)	9" (22.86)	25" (63.50)	03303017
2.50"-2.99" (6.35-7.59)	10,600 (47,149)	9" (22.86)	27" (68.58)	03303018
3.00"-3.49" (7.62-8.86)	14,700 (65,386)	10" (25.40)	30" (76.20)	03303019
3.50"-3.99" (8.89-10.13)	14,700 (65,386)	10" (25.40)	32" (81.28)	03303029



Junior Pulling Grips

Cable Diameter Range Inches (cm)	Approx. Breaking E Strength Lbs. (N)	E Inches (cm)	M Inches (cm)	Model	Catalog Numbers
.19"- .24" (.48-.61)	400 (1,779)	3 1/4" (8.25)	4 1/4" (10.79)	J19	03305011*
.25"- .36" (.63-.91)	450 (2,002)	3 1/4" (8.25)	4 1/4" (10.79)	J25	03305001
.37"- .49" (.94-1.24)	900 (4,003)	3 3/4" (9.52)	7" (17.78)	J37	03305002
.50"- .61" (1.27-1.55)	1,300 (5,782)	4 1/4" (10.79)	8 1/2" (21.59)	J50	03305003
.62"- .74" (1.57-1.88)	1,950 (8,674)	5" (12.70)	10" (25.40)	J62	03305004
.75"- .99" (1.90-2.51)	2,800 (12,454)	5 3/4" (14.60)	10" (25.40)	J75	03305005
1.00"-1.24" (2.54-3.15)	3,900 (17,347)	6 1/2" (16.51)	11 1/2" (29.21)	J100	03305006

E-Eye length M-Mesh length at nominal diameter.

*Not included in Junior Grip Kit, 033051114.