

RoHS Compliant

VX-001

EXPRESSCARD 1xRS232 1MBaud

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description

ExpressCard providing one RS232 serial port. Up to 921,600 data transfer rates and the 128 byte deep transmit and 256 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your laptop.

Low cost competitive range utilising USB technology. The most popular method of adding extra serial ports to your laptop.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

Features

- 1 port RS232
- USB 2.0
- 128 Byte Tx and 256 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Options



VX-001:
EXPRESSCARD 1xRS232
1MBaud

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows Vista 32 bit and 64 bit editions
- Windows XP 32 bit & 64 bit editions



As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.



ORDER

Description

EXPRESSCARD 1xRS232 1MBaud

Code



VX-001

* For 2 port RS232 see VX-012



EXPRESSCARD 1xRS232 1MBaud

VX-001: Full Specification

Port 	Ports Connector FIFO size Operating Distance Cable	1 x RS232 DB9 connector (9 Pin Male) 256 RX FIFO + 128 TX FIFO EIA - RS232 Standard No Cable; Integrated Connector
Port Settings 	Baud Rate Data Bits Parity Stop Bits Flow Control Tx/Rx Modes	921,600 7 or 8 Odd, Even, None, Mark or Space 1 or 2 RTS/CTS DSR/DTR XON/XOFF Point to Point
Interface 	OS Compatibility BUS	Windows Vista 32 bit & 64 bit Editions Windows XP 32 bit & 64 bit Editions USB 2.0 : 480 Mb/s USB 2.0 data rates
Approvals 	Other Approvals Microsoft Approvals	WEEE RoHS METL FCC Compliant Microsoft Certified Gold Partner Windows Vista 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions
General	PCB Layers Power Consumption Weight Size	4 40mA @ 3.3V 0.033 Kg 105x20x35 mm
Box Content	Packaging Card	Installation CD including manual, Microsoft signed drivers & utilities EXPRESSCARD 1xRS232 1MBaud No Cable; Integrated Connector
Product Support 	Warranty Support	Lifetime (online registration required) Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team
Additional 	OEM option Made In Customisable	Available for bulk buy OEM Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year" Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com