



UNIT:mm




CABLE WHITE PRINT
HI-SPEED USB Revision 2.0 SHIELDED 28AWG/1P+28AWG/2C
E189529 AWM STYLE 2725 80°C 30V VW-1 VEGA TECH

PIN ASSIGNMENT:



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: $2.0\text{m}\Omega(\text{max})$
3. Insulation resistance: $10\text{M}\Omega\text{m}(\text{min})$
4. dielectric test: DC 300V



			CnC Tech, LLC Industrial Cable and Connector Technology			
⑧	OUT JACKET	14.5g	BLACK 45P PVC (MOLD NO:CH003)			
	FERRITE	2	CORE OD12*5.6*L20 BLACK			
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"及印生产周期, 有透气孔.	DRAWN	LICHENG	DRAWING NO
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"及印生产周期, 有透气孔.	CHECKED		CUSTOMER
⑤	TIE	1	BLACK L=80mm			
④	OUT JACKET	12g	BLACK PVC-50P (MOULD NO:WM-40 & WM-88)	APPROVAL		ITEM NO.
③	CABLE	1	BLACK USB2.0 UL2725 28#/1P+28#/2C+AEB OD:3.8mm			
②	CONN	1set	USB2.0 刺破式 ATYPE MALE SHELL:NICKEL PIN:G/F 4PCS TYPE INSULATOR COLOR:WHITE	DECIDED		DATE
①	CONN	1set	USB2.0 刺破式 MINI 5P MALE SHELL:NICKEL PIN:G/F 3PCS INSULATOR COLOR:BLACK			
NO.	NAME	Q'TY	SPECIFICATION			
			VERSIONS/EDITION	A/0	PROJECTION	

4

3

2

1