

Ratings:
 Current 4A
 Voltage 150 V
 Wire Size 28-20AWG
 Test Voltage 1.25 kV

Rated Cross Section:
 Single Wire (solid) .5mm²
 Stranded Wire (flexible) on request
 Stranded Wire with Ferrules on request

Dimensions:
 Spacing 2.5mm (2.54mm)
 PCB Hole Diameter 1.1mm (2x)
 Stripped Length 5.0mm

Materials:
 Insulating Material PA
 Flammability UL94V-0
 Temperature -30°C/+105°C
 Tension Spring Stainless Steel
 Contact Cu
 Color Slade Gray (Orange)

