

# 3SMAJ5913B THRU 3SMAJ5943B

## 3.0 Watt Surface Mount Silicon Zener Diodes

### Features

- Surface Mount Application
- 3.3V thru 56 Volt Voltage Range
- Low Inductance , Low Profile Mounting
- Lead Free Finish/Rohs Compliant (Note1) ("P" Suffix designates Compliant. See ordering information)
- Glass Passivated Junction
- High specified maximum current (IZM) when adequately heat sinking

### Mechanical Data


- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Terminals solderable per MIL-STD-750, Method 2026
- Polarity is indicated by cathode band.
- Packaging: Standard 12mm Tape (see EIA 481)
- Maximum temperature for soldering: 260 °C for 10 seconds.

### Maximum Ratings @ 25°C Unless Otherwise Specified

|                                     |                |                 |           |
|-------------------------------------|----------------|-----------------|-----------|
| Maximum Forward Voltage             | $V_F$          | 1.5V            | (Note: 2) |
| Steady State Power Dissipation      | $P_d$          | 3.0W            | (Note: 3) |
| Operation and Storage Temperature   | $T_J, T_{STG}$ | -55°C to +150°C |           |
| Thermal Resistance Junction to Lead | $R_{thJL}$     | 25°C/W          |           |


- Note: 1. High Temperature Solder Exemptions Applied, see EU Directive Annex 7.  
2. Forward Current @ 200mA.  
3. Mounted on 5.0mm<sup>2</sup> (1oz thick) land areas.  
Lead temperature at  $T_L=75^\circ\text{C}$

### DO-214AC (SMA) (LEAD FRAME)



| DIMENSIONS |        |      |      |      |      |
|------------|--------|------|------|------|------|
| DIM        | INCHES |      | MM   |      | NOTE |
|            | MIN    | MAX  | MIN  | MAX  |      |
| A          | .079   | .096 | 2.00 | 2.44 |      |
| B          | .050   | .064 | 1.27 | 1.63 |      |
| C          | .002   | .008 | .05  | .20  |      |
| D          | ---    | .02  | ---  | .51  |      |
| E          | .030   | .060 | .76  | 1.52 |      |
| F          | .065   | .091 | 1.65 | 2.32 |      |
| G          | .189   | .220 | 4.80 | 5.59 |      |
| H          | .157   | .181 | 4.00 | 4.60 |      |
| J          | .090   | .115 | 2.25 | 2.92 |      |

### SUGGESTED SOLDER PAD LAYOUT



# 3SMAJ5913B thru 3SMAJ5943B

ELECTRICAL CHARACTERISTICS ( $T_L=30^{\circ}\text{C}$  unless otherwise noted) ( $V_F=1.5\text{Volts Max @ } I_F=200\text{mA}$  for all types.)

| MCC<br>PART<br>NUMBER | ZENER<br>VOLTAGE<br>$V_Z (1)$ | TEST<br>CURRENT<br>$I_{ZT}$ | MAXIMUM<br>DYNAMIC<br>IMPEDANCE<br>$Z_{ZT} @ I_{ZT}$ | KNEE<br>CURRENT<br>$I_{ZK}$ | KNEE<br>IMPEDANCE<br>$Z_{ZK}$ | MAXIMUM<br>REVERSE<br>CURRENT<br>$I_R$ | REVERSE<br>VOLTAGE<br>$V_R$ | Maximum<br>DC Zener<br>Current<br>$I_{ZM} \text{ mAdc}$ | DEVICE MARKING |
|-----------------------|-------------------------------|-----------------------------|------------------------------------------------------|-----------------------------|-------------------------------|----------------------------------------|-----------------------------|---------------------------------------------------------|----------------|
|                       | VOLTS                         | mA                          | OHMS                                                 | mA                          | OHMS                          | $\mu\text{A}$                          | VOLTS                       | mA                                                      |                |
| 3SMAJ5913B            | 3.3                           | 113.6                       | 10.0                                                 | 1.0                         | 500                           | 100                                    | 1.0                         | 908                                                     | H 13B          |
| 3SMAJ5914B            | 3.6                           | 104.2                       | 9.0                                                  | 1.0                         | 500                           | 75                                     | 1.0                         | 832                                                     | H 14B          |
| 3SMAJ5915B            | 3.9                           | 96.1                        | 7.5                                                  | 1.0                         | 500                           | 25                                     | 1.0                         | 768                                                     | H 15B          |
| 3SMAJ5916B            | 4.3                           | 87.2                        | 6.0                                                  | 1.0                         | 500                           | 5.0                                    | 1.0                         | 696                                                     | H 16B          |
| 3SMAJ5917B            | 4.7                           | 79.8                        | 5.0                                                  | 1.0                         | 500                           | 5.0                                    | 1.5                         | 638                                                     | H 17B          |
| 3SMAJ5918B            | 5.1                           | 73.5                        | 4.0                                                  | 1.0                         | 350                           | 5.0                                    | 2.0                         | 588                                                     | H 18B          |
| 3SMAJ5919B            | 5.6                           | 66.9                        | 2.0                                                  | 1.0                         | 250                           | 5.0                                    | 3.0                         | 534                                                     | H 19B          |
| 3SMAJ5920B            | 6.2                           | 60.5                        | 2.0                                                  | 1.0                         | 200                           | 5.0                                    | 4.0                         | 482                                                     | H 20B          |
| 3SMAJ5921B            | 6.8                           | 55.1                        | 2.5                                                  | 1.0                         | 200                           | 5.0                                    | 5.2                         | 440                                                     | H 21B          |
| 3SMAJ5922B            | 7.5                           | 50.0                        | 3.0                                                  | 0.5                         | 400                           | 5.0                                    | 6.0                         | 400                                                     | H 22B          |
| 3SMAJ5923B            | 8.2                           | 45.7                        | 3.5                                                  | 0.5                         | 400                           | 5.0                                    | 6.5                         | 364                                                     | H 23B          |
| 3SMAJ5924B            | 9.1                           | 41.2                        | 4.0                                                  | 0.5                         | 500                           | 5.0                                    | 7.0                         | 328                                                     | H 24B          |
| 3SMAJ5925B            | 10                            | 37.5                        | 4.5                                                  | 0.25                        | 500                           | 5.0                                    | 8.0                         | 300                                                     | H 25B          |
| 3SMAJ5926B            | 11                            | 34.1                        | 5.5                                                  | 0.25                        | 550                           | 1.0                                    | 8.4                         | 272                                                     | H 26B          |
| 3SMAJ5927B            | 12                            | 31.2                        | 6.5                                                  | 0.25                        | 550                           | 1.0                                    | 9.1                         | 250                                                     | H 27B          |
| 3SMAJ5928B            | 13                            | 28.8                        | 7.0                                                  | 0.25                        | 550                           | 1.0                                    | 9.9                         | 230                                                     | H 28B          |
| 3SMAJ5929B            | 15                            | 25.0                        | 9.0                                                  | 0.25                        | 600                           | 1.0                                    | 11.4                        | 200                                                     | H 29B          |
| 3SMAJ5930B            | 16                            | 23.4                        | 10.0                                                 | 0.25                        | 600                           | 1.0                                    | 12.2                        | 186                                                     | H 30B          |
| 3SMAJ5931B            | 18                            | 20.8                        | 12.0                                                 | 0.25                        | 650                           | 1.0                                    | 13.7                        | 166                                                     | H 31B          |
| 3SMAJ5932B            | 20                            | 18.7                        | 14.0                                                 | 0.25                        | 650                           | 1.0                                    | 15.2                        | 150                                                     | H 32B          |
| 3SMAJ5933B            | 22                            | 17.0                        | 17.5                                                 | 0.25                        | 650                           | 1.0                                    | 16.7                        | 136                                                     | H 33B          |
| 3SMAJ5934B            | 24                            | 15.6                        | 19.0                                                 | 0.25                        | 700                           | 1.0                                    | 18.2                        | 124                                                     | H 34B          |
| 3SMAJ5935B            | 27                            | 13.9                        | 23.0                                                 | 0.25                        | 700                           | 1.0                                    | 20.6                        | 110                                                     | H 35B          |
| 3SMAJ5936B            | 30                            | 12.5                        | 28.0                                                 | 0.25                        | 750                           | 1.0                                    | 22.8                        | 100                                                     | H 36B          |
| 3SMAJ5937B            | 33                            | 11.4                        | 33.0                                                 | 0.25                        | 800                           | 1.0                                    | 25.1                        | 90                                                      | H 37B          |
| 3SMAJ5938B            | 36                            | 10.4                        | 38.0                                                 | 0.25                        | 850                           | 1.0                                    | 27.4                        | 82                                                      | H 38B          |
| 3SMAJ5939B            | 39                            | 9.6                         | 45.0                                                 | 0.25                        | 900                           | 1.0                                    | 29.7                        | 76                                                      | H 39B          |
| 3SMAJ5940B            | 43                            | 8.7                         | 53.0                                                 | 0.25                        | 950                           | 1.0                                    | 32.7                        | 68                                                      | H 40B          |
| 3SMAJ5941B            | 47                            | 8.0                         | 67.0                                                 | 0.25                        | 1000                          | 1.0                                    | 35.8                        | 62                                                      | H 41B          |
| 3SMAJ5942B            | 51                            | 7.3                         | 70.0                                                 | 0.25                        | 1100                          | 1.0                                    | 38.8                        | 58                                                      | H 42B          |
| 3SMAJ5943B            | 56                            | 6.7                         | 86.0                                                 | 0.25                        | 1300                          | 1.0                                    | 42.6                        | 52                                                      | H 43B          |

Note 1: TOLERANCE AND VOLTAGE DESIGNATION - The type numbers listed indicate a tolerance of +/- 5%.

## RATING AND CHARACTERISTICS CURVES




Fig. 1-STEADY STATE POWER DERATING




Fig. 2-ZENER VOLTAGE- 3 TO 12 VOLTS

**M.C.C.**  
Micro Commercial Components




Fig. 3-ZENER VOLTAGE-10 TO 200 VOLTS

Fig. 4-EFFECT OF ZENER CURRENT






Fig. 7-VZ = 12 THRU 40 VOLTS



Micro Commercial Components

## Ordering Information :

| Device         | Packing                 |
|----------------|-------------------------|
| Part Number-TP | Tape&Reel: 7.5Kpcs/Reel |

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

[www.mccsemi.com](http://www.mccsemi.com)