


Part # CB-30, Double Contact Candelabra Bayonet Lampholders

Steel Zinc Plated shell and bracket with steel zinc plated spring, brass nickel plated contacts, 18 Awg UL 200C wires. UL rated 125V 75W. With 1/8" NPSM threaded bushing 1/4" long



SPECIFICATIONS

|                |            |
|----------------|------------|
| Bulb Base      | BA15D      |
| Wattage Rating | 75 W       |
| Voltage Rating | 125 V      |
| Wire           | 18AWG 105C |
| UL Approved    | ✓          |
| Minimum Order  | 20         |