


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1M-186	.13 (3.3)	.87 (22)	.044 (1.1)	.098 (2.5)	.159 (4.0)	.186 (4.7)	.188 (4.8)	3.9 (100)	15 (67)	MINIATURE	CURVED	.06 (28)
PLT2I-186	.13 (3.3)	2.00 (51)	.047 (1.2)	.135 (3.4)	.200 (5.1)	.180 (4.6)	.240 (6.1)	8.0 (203)	24 (107)	INTERMEDIATE	CURVED	.18 (81)
PLT2S-186	.13 (3.3)	1.85 (47)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.30 (186)	30 (133)	STANDARD	CURVED	.30 (138)
PLT3S-186	.13 (3.3)	3.00 (76)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	11.50 (291)	30 (133)	STANDARD	CURVED	.47 (213)
PLT4S-186	.13 (3.3)	4.00 (102)	.057 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	14.40 (366)	30 (133)	STANDARD	CURVED	.60 (274)
PLT3H-186	.25 (6.4)	3.00 (76)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	11.10 (282)	60 (267)	LIGHT-HEAVY	STRAIGHT	.99 (448)
PLT4H-186	.25 (6.4)	4.00 (102)	.075 (1.9)	.300 (7.6)	.370 (9.4)	.360 (9.1)	.480 (12.2)	14.40 (366)	60 (267)	LIGHT-HEAVY	STRAIGHT	1.20 (544)

W10001C1/00

NOTES:

- 1) SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2) COMPOSED OF METAL DETECTABLE POLYPROPYLENE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES
PLT METAL DETECTABLE
POLYPROPYLENE SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .005 (XXX) ± .020 (51)
(.XX) ± .021 (51) ANGLES ± .005

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
ERW

MAT'L:

SCALE
NONE

DATE
8/18/08

METAL DETECTABLE
POLYPROPYLENE
COLOR: BLUE

DRAWING NO.
SS-27604

DWG
A
SIZE

R	8/18/08	ERW		DRAWING RELEASED			27604	R				
REV	DATE	BY	CHK	DESCRIPTION			ECN - R	CUST	SUP			