







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT JACKETED FIBER PATCH
CORD MASTER OPTIONS LIST



1st POSITION - FIBER PRODUCT

F - FIBER

2nd POSITION - FIBER TYPE

- 9 - SINGLEMODE
- S - SIG-CORE (OM4+)
- X - OM3
- Z - OM4

3rd POSITION - FIBER COUNT

2 - 2 FIBER

4th POSITION - CABLE TYPE

- E - 1.6mm DUPLEX
- 3 - 3mm DUPLEX (SC-SC ONLY)

5th POSITION - JACKET TYPE

- P - PLENUM
- R - RISER
- L - LSZH

6th POSITIONS - CONNECTOR (END A)

- Q - PUSH PULL DUPLEX LC
- L - LC DUPLEX
- S - SC DUPLEX

7th POSITIONS - CONNECTOR VARIANT

- 1 - PUSH PULL DUPLEX LC
- N - NO VARIANT

8th POSITION - CONNECTOR (END B)

- Q - PUSH PULL DUPLEX LC
- L - LC DUPLEX
- S - SC DUPLEX

9th POSITIONS - CONNECTOR VARIANT

- 1 - PUSH PULL DUPLEX LC
- N - NO VARIANT

10th POSITION - PERFORMANCE/POLARITY

- S - STANDARD IL
- T - STANDARD IL PAIR FLIPPED
- O - OPTIMIZED IL
- P - OPTIMIZED IL PAIR FLIPPED
- N - ULTRA LOW IL (OM4 & OM4+ ONLY)

11th POSITION - PULLING EYE


N - NO PULLING EYE

12th POSITION - UNIT OF MEASURE

- F - FEET
- M - METERS

13th, 14th, AND 15th POSITIONS - ASSEMBLY LENGTH

- F - 001-050 FEET
- M - 001-050 METERS

							TITLE JACKETED DUPLEX FIBER PATCH CORDS					
							CUSTOMER DRAWING					
							ITEM REVISION NAME M02779DX/00					
							DATASET FILE NAME M02779DX_DC/00B					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.762] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 1 °			MATERIAL :		
01	07-06-16	SAT	RWB	MMN	SEE SHEET 1 FOR REVISION HISTORY.	M02779DX-DC	 THIRD ANGLE PROJECTION			DRAWING NUMBER: M02779DX-DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 01-04-16	CHK RWB	SCALE NONE	SHT 2 OF 2	SIZE B

