


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PART NO.    | PANDUIT TUBING P/N | COLOR  | Part Description                     | TUBING +/- 0.050 WIDTH "A" | ROLL LENGTH |
|-------------|--------------------|--------|--------------------------------------|----------------------------|-------------|
| H000X025F1C | GMHS31             | WHITE  | 1/8" dia. H.S. Polyolefin 22-16 AWG  | .25 [6.35] REF.            | 96.0"       |
| H000X034F1C | GMHS31             | WHITE  | 3/16" dia. H.S. Polyolefin 18-12 AWG | .34 [8.64] REF.            | 96.0"       |
| H000X044F1C | GMHS31             | WHITE  | 1/4" dia. H.S. Polyolefin 16-10 AWG  | .44 [11.18] REF.           | 72.0"       |
| H000X084F1C | GMHS31             | WHITE  | 1/2" dia. H.S. Polyolefin 8-1 AWG    | .84 [21.34] REF.           | 72.0"       |
| H000X025H1C | GMUHS31            | WHITE  | 1/8" dia. H.S. Polyolefin 22-16 AWG  | .25 [6.35] REF.            | 96.0"       |
| H000X034H1C | GMUHS31            | WHITE  | 3/16" dia. H.S. Polyolefin 18-12 AWG | .34 [8.64] REF.            | 96.0"       |
| H000X044H1C | GMUHS31            | WHITE  | 1/4" dia. H.S. Polyolefin 16-10 AWG  | .44 [11.18] REF.           | 72.0"       |
| H000X064H1C | GMUHS31            | WHITE  | 3/8" dia. H.S. Polyolefin 12-6 AWG   | .64 [16.26] REF.           | 72.0"       |
| H000X084H1C | GMUHS31            | WHITE  | 1/2" dia. H.S. Polyolefin 8-1 AWG    | .84 [21.34] REF.           | 72.0"       |
| H000X025H2C | GMUHS31            | YELLOW | 1/8" dia. H.S. Polyolefin 22-16 AWG  | .25 [6.35] REF.            | 96.0"       |
| H000X034H2C | GMUHS31            | YELLOW | 3/16" dia. H.S. Polyolefin 18-12 AWG | .34 [8.64] REF.            | 96.0"       |
| H000X044H2C | GMUHS31            | YELLOW | 1/4" dia. H.S. Polyolefin 16-10 AWG  | .44 [11.18] REF.           | 72.0"       |
| H000X064H2C | GMUHS31            | YELLOW | 3/8" dia. H.S. Polyolefin 12-6 AWG   | .64 [16.26] REF.           | 72.0"       |
| H000X084H2C | GMUHS31            | YELLOW | 1/2" dia. H.S. Polyolefin 8-1 AWG    | .84 [21.34] REF.           | 72.0"       |



NOTES:  
1. DIMENSIONS IN [ ] ARE IN MILLIMETERS.

|     |         |     |     |                                  |      |     |      |     |  |                                                                                                                          |                         |                                                                                               |                  |
|-----|---------|-----|-----|----------------------------------|------|-----|------|-----|--|--------------------------------------------------------------------------------------------------------------------------|-------------------------|-----------------------------------------------------------------------------------------------|------------------|
|     |         |     |     |                                  |      |     |      |     |  | 100743CM-DC-C10692/06B                                                                                                   |                         |                                                                                               |                  |
|     |         |     |     |                                  |      |     |      |     |  | PANDUIT CORP. TINLEY PARK, ILLINOIS                                                                                      |                         |                                                                                               |                  |
|     |         |     |     |                                  |      |     |      |     |  | CUSTOMER DRAWING<br>P1 LABEL CASSETTE<br>CONTINUOUS HEAT SHRINK                                                          |                         |                                                                                               |                  |
|     |         |     |     |                                  |      |     |      |     |  | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ± .1      (.XXX) ± .025<br>(.XX) ± .050      ANGLES ± |                         | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |                  |
| 1   | 5/21/10 | RVU |     | ADD H000X064H1C AND H000X064H2C. | 5992 | R   |      |     |  | DRAWN BY<br>RVU                                                                                                          | MAT'L;<br><br>SEE TABLE | SCALE<br>FULL                                                                                 |                  |
| 0   | 4/21/08 | RVU |     | DRAWING RELEASE                  | 5403 | R   |      |     |  | DATE<br>4/22/08                                                                                                          |                         | DRAWING NO.<br>C10692                                                                         | DWG<br>A<br>SIZE |
| REV | DATE    | BY  | CHK | DESCRIPTION                      | ECN  | - R | CUST | SUP |  | CHK'D                                                                                                                    |                         |                                                                                               |                  |