



Datasheet for part number CA3102E24-6SX

Our Catalog Part Number: CA3102E24-6SX	
Brand: Cannon	Product Category: Circular Product Line: MIL-DTL 5015 Series I Series: MIL-C-5015

Product Datasheet	
Thread	Connector with threaded coupling
Shell Style	Box mounting receptacle
Gender	Socket
Shell Size	24
Contact Arrangement	24-6
Number of contacts	3 contacts size 12
Contact Type	Solder Cup
Contact Plating	Hard silver
Shielding	no
Insulator Rotation	110°
Contact Rating at +20 °C (68 °F) (Size 25/12)	41 A
Contact Resistance (Size 25/12)	3 mΩ
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Insulator Resistance	Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ
Test Voltage	1600 Vrms
Air and Creepage Paths (Min)	1,1 mm
Ambient Temperature	Standard insulator material -55°/+125°C (-67/257°F)
Safety Provisions	IP67 acc. to DIN 40 050 (1 bar pressure after 12 hrs)
Salt Spray Resistance	500 hours salt spray resistant
Mating Cycles	500 min
Sep. Force per Contact (Size 25/12)	1,5 N
Gage	For infos on Gage please see catalog VG95234, part 1
Coupling Torque	Closing: 14 Nm max / Opening: 0,8 Nm min
Contact Retention (Size 25/12)	55 N
Shell Material	Aluminium alloy
Shell Plating	Olive drab chromate coating over cadmium plating
Insulator and Gromet Material	Neoprene
Contact Material	Copper alloy
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction
Wire Stripping (Size 25/12)	6,2 mm
General Info	<i>All tests in accordance with VG95319 and/or if applicable with VG95210</i>