











- 3 一般公差: ± 0.1
- 4 コプラナリティ: 0.08mm 以下とする
- 5 材料はテーブル参照のこと
- 6 仕上げはテーブル参照のこと
- 7 バリなき事
- 8 その他の詳細は別途打合せのこと
- 3 GENERAL TOLERANCE: ± 0.1
- 4 MUST BE MEASURED FLOATING AMOUNT OF TINES AND SOLDER PEG ROM DATUM SURFACE IS 0.08mm MAX.
- 5 MATERIAL THE TABLE IS REFERENCE
- 6 FINISH THE TABLE IS REFERENCE
- 7 NO BURRS ALLOWED
- 8 IN ADDITION DETAILS ARE THE SEPARATE HITTING ADJUSTING



Ni; 1.3um MIN., TIN; 2.0um MIN.	COOPER ALLOY	SOLDER PEG	3
	THERMO PLASTIC	HOUSING	2
Ni; 1.3um MIN., Au; 0.1um MIN. (CONTACT POINT) Ni; 1.3um MIN., Au; 0.05um ~0.20um. (TINE)	COPPER ALLOY	CONTACT	1
FINISH 6	MATERIAL 5	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL
材料 5

FINISH
仕上 6

DWN

CHK

APVD

PRODUCT SPEC
製品規格
108-5901

APPLICATION SPEC
取付適用規格
411-78159

WEIGHT

CUSTOMER DRAWING

NAME
名称

0.4mm PITCH STACKING CONNECTOR
H=1.0mm RECEPTACLE,
S2 TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-1747769

RESTRICTED TO

SCALE
尺度 15:1

SHEET
2 OF 2

REV
L1

TE Connectivity