



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
		D		REV PER ECR 10-000722	25JAN10	JR
						APVD
						TM



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 2/OW* 125, APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0.00254 [.000100] MIN THK EXT. PER ASTM B-545
- 4 MAX RECOMMENDED OPERATING TEMP IS 170°C.
- 5 WIRE CROSS SECTIONAL AREA RANGE: 60.6-76.3mm [119,500-150,500] CMA SOLID OR STRANDED.



50	LOOSE PIECE	322224
QTY	PACKAGING TYPE	PART NO.
Tyco Electronics Corporation Harrisburg, PA 17105-3608		
NAME		
TERMINAL, RING TONGUE, SOLISTRAND		
SIZE	CAGE CODE	DRAWING NO
A2	00779	C=322224
RESTRICTED TO	SCALE	SHEET
-	2:1	1 of 1
REV	D	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	DK SCHRUM	8/4/93
		CHK	AJ KAUFMAN	8/5/93
		APVD	JL MECKLEY	8/5/93
		PRODUCT SPEC		
		APPLICATION SPEC		
		WEIGHT	-	
		CUSTOMER DRAWING		

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
MM [INCHES]	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± 0.20[.008]
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
	FINISH
MATERIAL	
- 2	- 3