

# PCB Terminal Blocks

## 0488660000

When good enough just isn't good enough

**Weidmüller** 

TOP 1.5GS/5.08/90, single level, 90° orientation

[Email to a Friend](#)[View Line Drawing](#)

Representative Photo

### Technical Information

Pitch	5.08 mm
Clamp Type	TOP Connection
Orientation	90°
Configuration	Single Level
Poles	3
Current	10 A
Voltage	300 V
Wire Size	#26...14 AWG
Test Points	No
Color	Orange

### Technical Data

	UL	CSA	VDE
Rated Voltage	300 V	300 V	250 V
Rated Current	10 A	10 A	16 A
Wire Size	#22...14 AWG	#22...14 AWG	1.5 mm <sup>2</sup>
Strip Length	10 mm	10 mm	10 mm
Torque Nm (lb. in.)	0.5 (4.4)	0.5 (4.4)	0.5 (4.4)
Pin Length	3.5 mm	3.5 mm	3.5 mm

### Additional Data

Molding Material	Polyamide
Flammability Class	UL 94 (V2)
Contact	Copper alloy
Plating	Tin-Plated
Temperature Range	-50°C (-58°F) - +100°C (+212°F)
PCB Mounting Hole Diameter	1.3 <sup>+0.1</sup> mm
Clamping Screw	M 3

## Suggested Accessories

KSW marking strips

Locking blocks

Screwdrivers

**Product Liability** The above information describes our products. It does not constitute guaranteed properties and is not intended to affirm the suitability of a product for a particular application. Regrettably, omissions and exceptions cannot be completely ruled out. Technical data are always specified by their average values. Exact data and the tolerances which apply to our processes can be requested from:

Weidmüller - North America  
United States 001 (800) 849-9343  
Canada 001 (800) 268-4080

or

Weidmüller - Germany  
Telephone operator 0049 (-5252) 960-0