

MINIATURE LAMP (912) Details



Part #	912				
Description	T5 WEDGE 12.8V 1A 12CP				
Bulb Shape	T-5	Filament	C-2R	Base Style	Wedge (T-5)
Glass Diameter (in)	0.63	MOL [†] (in)	1.49	LCL ^{††} (in)	0.81
Glass Diameter (mm)	16	MOL (mm)	37.80	LCL (mm)	20.60
Volts	12.8	MSCP [‡]	12	Avg Life Hrs	1000
Watts	12.8	Amps	1.00	RoHS Compliant	Yes

[†] MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

[‡] MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

^{††} LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.