

Models 6854 XLR (F) 5-pin Rectangular Flanged Panel Mount



Model 6854 XLR (F) 5-pin rectangular flanged mount

Protect contacts and absorb vibrations in your audio applications.

Features


- 3-pin XLR panel mount with sturdy all metal one piece design.
- Solder cup terminations.
- Low contact resistance.
- Front mountable.

Materials

- Housing is die cast zinc alloy with tarnish resistant nickel plating.
- Contacts are bronze with tin finish (Ground tab is steel).

Ordering Information

Model: 6854.



Specifications

Number of contacts	5
Contact resistance	< 5 mΩ
Dielectric strength	1500 V dc
Wire size (AWG)	18 AWG (2.0 mm ²) max.

USA: Sales: 800-490-2361 Technical Support: 800-241-2060 Fax: 888-403-3360

Europe: 31-(0) 40 2675 150 International: 425-446-5500

e-mail: technicalsupport@pomonatest.com

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.