



OGA DIAGONAL: 7.53 [191.20]
VA DIAGONAL: 6.71 [170.43]
PA DIAGONAL: 6.36 [161.53]



TOP LEVEL NUMBER	US NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8091-203	98-0003-2549-2	FFC	4.27" [108.46]	AG500	23655
17-8091-204	98-0003-2550-0	FFC	6.00" [152.40]	AG500	23655
17-8091-205	98-0003-2551-8	FFC	8.00" [203.20]	AG500	23655
17-8091-206	98-0003-2552-6	NOV	SEE DWG	AG500	23655
17-8091-221	98-0003-2555-9	SER	4.27" [108.46]	AG500	23655
17-8091-223	98-0003-2556-7	SER	6.00" [152.40]	AG500	23655
17-8091-227	98-0003-2558-3	SER	8.00" [203.20]	AG500	23655
17-8091-218	98-0003-2933-8	USB R	4.27" [108.46]	AG500	23655
17-8091-226	98-0003-2934-6	USB R	8.00" [203.20]	AG500	23655


NOTES:

- WEIGHT OF GLASS IN GRAMS: 134±10%
- NICOMATIC HOUSING P/N: 0LO5
NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
HOUSING ORIENTED WITH LATCH DOWN



PINOUT	
1	LR
2	LL
3	SHIELD
4	UL
5	UR

UNITS	INCHES [MM]
TOLERANCES UNLESS OTHERWISE SPECIFIED	
.X	±
.XX	±.03 [.76]
.XXX	±.015 [.38]
ANGLES	±1°



DO NOT SCALE DRAWING
SCALE 1 = 1

3M 3M TOUCH SYSTEMS
METHUEN, MA
USA
© COPYRIGHT 2005
THIS DOCUMENT IS COPYRIGHTED PROPERTY OF THE
3M COMPANY AND MAY NOT BE REPRODUCED
WITHOUT 3M WRITTEN PERMISSION OR USED OR
DISCLOSED FOR OTHER THAN 3M AUTHORIZED
PURPOSES.

DRAWN K. CROWLEY 9/05

H	REVISED PER CO 036256	4/13	SB
G	REVISED PER CO 033533	2/12	SB
F	REVISED PER CO 033535	9/11	SB
REV	CHANGE NOTICE	DATE	DRW

TITLE MARKETING DRAWING SCT32NN 6.71"			
CAD FORMAT	AUTOCAD	SHEET	1 OF 1
SIZE	DOCUMENT NO.	REV	
C	28406-MKT	H	