



				1						
LOC	DIST	P	F	REVISIONS						
FT	13			ZONE	LTR	DESCRIPTION			DATE	APPD
					N	REDRAWN & REV PER BD6076			03/11/92	—
					P	REV PER EC 0320-135-97			06 MAY 97	MM



- 1

NYLON, UL 94V-0 RATED, RED.
- 2

BRASS PER ASTM B36.
- 3

3.81µm [.000150] MIN TIN OVER 2.54µm [.000100] MIN COPPER.
- 4

0.76µm [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.
- 5

SELECTIVELY LOADED CONTACTS IN POSITIONS 1 THRU 5, 7 THRU 12.

		3	YES	5	207120-7	
		4	NO		207120-4	
		4	YES		207120-3	
		3	NO		207120-2	
		3	YES		207120-1	
		CONTACT FINISH	MOUNTING TABS	PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.25 [.010] 3 PLC DEC ± - ANGLES ± - MATERIAL HOUSING: 1 CONTACT: 2		DR 03/11/92 L.SIPE		AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK 3-17-92 R.STONE				
		APPD 3-17-92 A.TRAVIS		NAME PIN HEADER ASSEMBLY, 12 POSITION, METRIMATE		
		APPD 3-18-92 C.ROHDE				
		PRODUCT SPEC 108-10033				
FINISH CONTACT: SEE TABLE		APPLICATION SPEC -		SIZE C	CAGE CODE 00779	DRAWING NO 207120
		WEIGHT -		SCALE 4:1		SHEET 1 OF 1