

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002061110

Status:

Obsolete

Overview:


standard_062

Description:

1.57mm (.062") Diameter, Standard .062" Pin and Socket Crimp Terminal, Series 4559, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 24-30 AWG, Bag Packaged

Replacement Part Number:

NONE



Series

image - Reference only

Documents:
[Drawing \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	4559
Application	Power
Crimp Quality Equipment	Yes
Obsolete Date	2003/01/01
Overview	standard_062
Product Name	Standard .062"
Replacement Part Number	NONE

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Bag
Plating min - Mating	0.508µm (20µ")
Plating min - Termination	0.508µm (20µ")
Wire Insulation Diameter	1.02-2.29mm (.040-.090")
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Old Part Number	4559-P901-L
-----------------	-------------

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
4559Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Manual Extraction Tool	0011030002

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION