




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B	REVISED PER ECO-14-011808	11AUG2014	AP	SB

D




- 1 MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK.
SHELLS & BRACKETS: CARBON STEEL.
CONTACTS: BRASS
- 2 SHELLS: .000200 MIN TIN OVER .000100 MIN COPPER.
BRACKETS: .000200 MIN TIN OVER .000050 MIN COPPER.
CONTACTS: GOLD PLATING FOR A LENGTH OF .150 MIN FROM MATING END, .000030 MIN GOLD IN MATED AREA, .000100 MIN TIN ON OPPOSITE END, BOTH OVER .000050 MIN NICKEL.
-OR-
GOLD FLASH OVER PALLADIUM NICKEL PLATED FOR A LENGTH OF .150 MIN FROM MATING END, .000030 MIN PALLADIUM NICKEL IN MATED AREA, .000100 MIN TIN ON OPPOSITE END, BOTH OVER .000050 MIN NICKEL.

C



B



P.C. BOARD MOUNTING DIMENSIONS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HENNY 8-24-05	 TE Connectivity			
DIMENSIONS: INCHES		CHK S. BOLASH 8-24-05				
		APVD M. WALMSLEY 8-24-05	NAME			
		PRODUCT SPEC 108-40025	PLUG ASSY, SIZE 1, 9 POSITION, RIGHT ANGLE, .545 SERIES, .025 SQ POSTS, AMPLIMITE HDP			
MATERIAL		APPLICATION SPEC 114-40013	SIZE A2	CAGE CODE 00779	DRAWING NO C=5745351	RESTRICTED TO —
FINISH		WEIGHT —	SCALE 4:1		SHEET 1 of 1	REV B
		CUSTOMER DRAWING				