



Non-Metallic Conduits

• HG-DC Double Slit

Double slit corrugated conduit for retrofitting.

Features and Benefits

- Can be opened and closed repeatedly
- Cables can be inserted laterally
- Abrasion resistant
- Free of halogen, sulphur and phosphorus
- Colour: black (UV resistant)

Application

Control panels, machine building, plant construction and wherever retrofitting is a requirement.



HelaGuard HG-DC double slit conduit is ideal for retrofitting.

Material Data

Material	Polyamide 6 (PA6)
Operating Temperature	-40 °C to +110 °C
Flammability	UL94 V2



Technical Table

Article-No.	Type	Nominal Ø	Outside Ø	Ø D	Bending Radius	Weight (g/m)	Reel Length (m)	Colour
166-11800	HG-DC11	11	11.2	6.7	45	23	50	Black (BK)
166-11801	HG-DC13	13	12.9	7.9	55	37	50	Black (BK)
166-11802	HG-DC16	16	15.8	10.5	60	41	50	Black (BK)
166-11803	HG-DC21	21	21.0	13.9	90	63	50	Black (BK)
166-11804	HG-DC28	28	28.3	20.5	105	94	50	Black (BK)
166-11805	HG-DC34	34	34.5	27.0	150	118	25	Black (BK)
166-11806	HG-DC42	42	42.5	34.8	170	193	25	Black (BK)
166-11807	HG-DC54	54	54.5	45.3	170	263	25	Black (BK)

All dimensions in mm. Subject to technical changes.

Other reel lengths available on request.