




DIMENSIONS

mm (inches)

 $88^{+0}_{-0.2}$ (3.464) $(.457 \text{ max})$
11.6 maxi ± 0.06
5.08
(.200) $85.2^{+0.2}_0$ (3.354) $\phi 2.8 \text{ mini}$
(.110) $0.3^{+0.1}$
(.012)

TIN LEAD

LEAD FREE

8609 396 78 14 745 000 E1	8609 396 78 14 745 E1 LF	Style R header, 96 Position, solder to board, class 3
8609 396 78 14 755 000 E1	8609 396 78 14 755 E1 LF	Style R header, 96 Position, solder to board, class 2
8609 396 78 14 765 000 E1	8609 396 78 14 765 E1 LF	Style R header, 96 Position, solder to board, class 1
8609 464 78 14 745 000 E1	8609 464 78 14 745 E1 LF	Style R header, 64 Position, solder to board, class 3
8609 464 78 14 755 000 E1	8609 464 78 14 755 E1 LF	Style R header, 64 Position, solder to board, class 2
8609 464 78 14 765 000 E1	8609 464 78 14 765 E1 LF	Style R header, 64 Position, solder to board, class 1

Application specific part-numbers: See sheet 2

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C-8609-0000A

rev	ecn no	dr	date
C	-	ROU	2002/08/28
D	LS05-001	JTA	2005/03/01
E	LS06-0089	LGO	2006/06/01
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	ROUILLARD	23/06/92	ANGULAR LINEAR	0.X		± 0.1		size A3	Scale 1.5:1	
Eng	LEGALLIC	23/06/92		0.XX		± 0.1			ECN LS06-0089	
Chr	LEGARE	23/06/92		0.XXX		± 0.1				
Appr	LEGARE	23/06/92	0.XX' ±2"							
			Product family				DIN		Spec ref -	
			title STRAIGHT HEADER- STYLE R SOLDER TO BOARD				dwg no C-8609-0265-1			Rev. E
			catalog no				-		CUSTOMER sheet 1 of 2	

B

C



D

D

P