



REVISIONS									
NO	LOC	DATE	BY	ZONE	LTR	DESCRIPTION	DATE	APPD	
85	AR	39				D REDAWN PER ECN AR 2252	1/17/89	KIH	
						E REV PER ECN 803782	4-2-90	JFY	

1. HOUSING WILL ACCOMMODATE FLEXIBLE, FLAT CONDUCTOR CABLE
.050 OR .062 WIDE CONDUCTORS ON .100 CENTERS AND/OR #32-22 AWG
WIRE WITH INSULATION RANGE .040-.069 DIA.
- △ CAVITY IDENTIFICATION FOR FIRST POSITION.
- △ AMP TRADEMARK MOLDED IN AREA SHOWN
- △ PIN CONTACTS MUST BE ORDERED SEPARATELY.
- △ CUSTOMER PART NO, FIRST & LAST POSITION NO TO BE INK STAMPED
WITH WHITE INK, LOCATED APPROXIMATELY AS SHOWN.



SECTION X-X
CRIMPED CONTACT SHOWN
FOR REF ONLY

713W72120	1.760	1.510	1.250	1.126	1.160	1.040	9	10	494031-4
713W72020	1.260	1.010	.750	.626	.660	.540	4	5	494031-2
CUSTOMER PART NUMBER	F	E	D	C	B	A	NO. OF SPACES	NO. OF POSN	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± - MATERIAL THERMOPLASTIC FLAME RETARDANT COLOR: BLACK FINISH -							AMP AMP INCORPORATED Harrisburg, Pa. 17105		
DR 1/17/89 KATE HELM CHK 3-3-89 D.ROCKER APPD 3-3-89 G.D.MILLER APPD 3-3-89 W.PARKER PRODUCT SPEC - APPLICATION SPEC - WEIGHT -							NAME HSG, PIN, SHROUDED, W/MTG EARS, .100¢, FFC		
							SIZE D	FSCM NO 00779	DRAWING NO 494031
							SCALE 4:1	SHEET TSNOF TOF	